



SPOS Spring Post

[WEB Selection Tool](#)
[WEB CAD Download](#)
SUS Stainless steel

SPOS-A



SPOS-B



- Post for tensile coil spring.
- There are bore type and groove type. ◀ 3

SPOS-A ——— Bore type

SPOS-B ——— Groove type

- Material/Finish

RoHS Compliant

	SPOS
Main body	SUS303

SPOS-A Bore type

Unit : mm

Part Number	M (coarse) ◀ 1	L ◀ 2	L ₁	D	F	d	T	Mass (g)
SPOS-M3-10-A	M3	10	5	3	3	1.5	1.2	0.6
SPOS-M3-15-A	M3	15	10	3	3	1.5	1.2	0.9
SPOS-M4-15-A	M4	15	10	4	3	2	1.2	1.5
SPOS-M4-20-A	M4	20	10	4	3	2	1.2	2
SPOS-M4-25-A	M4	25	10	4	3	2	1.2	2.5
SPOS-M5-20-A	M5	20	10	5	5	2	1.2	3.5
SPOS-M5-25-A	M5	25	10	5	5	2	1.2	4
SPOS-M5-30-A	M5	30	10	5	5	2	1.2	4.5
SPOS-M6-25-A	M6	25	16	6	5	2	1.2	6.8
SPOS-M6-30-A	M6	30	16	6	5	2	1.2	7.4
SPOS-M6-40-A	M6	40	16	6	5	2	1.2	8

Cleanroom Wash & Packaging → P.792	Screw Length Adjustment → P.796	Vibration Resistant → P.795	Laser Marking → P.806
Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Not Available