


SWUT Hex Lock Nuts - Titanium



[WEB Selection Tool](#)
[WEB CAD Download](#)
[Cleanroom wash & packaging](#)
[Non-Magnetic](#)
[Lightweight](#)
[Vibration resistant treatment](#)



- Specific gravity is approximately 60% of stainless steel.
- These nuts are equipped with vibration resistant patch to prevent screw from loosening.
- Continuous Max. Operating Temperature : -40 to 120 deg C

Application

Lightweight applications in automobiles, aircrafts, spacecrafts, and robots FPD production equipment, semiconductor devices, electrical and electronic equipment, and loosening prevention

Material/Finish



	SWUT
Main Body	FRS-9901 (Equivalent to TW340)
Nylon Ring	Nylon 66

Unit : mm

Part Number	M	B	C (Approx.)	T	Mass (g)	Qty per pack
SWUT-M3	M3	5.5	6.4	4	0.27	1
SWUT-M4	M4	7	8.1	5	0.52	1
SWUT-M5	M5	8	9.2	6.5	0.77	1
SWUT-M6	M6	10	11.5	8	1.8	1
SWUT-M8	M8	13	15	9.8	3.5	1
SWUT-M10	M10	17	19.6	12	7.3	1

Related Products

SWUS Hexagon Lock Nut made of stainless steel is available.
 → P.782



Part number specification

SWUT-M6



1 Individual Sales → P.794	Cleanroom Wash & Packaging → P.792	Screw Length Adjustment → P.796	Vibration Resistant → P.795	Modification process for captive use → P.791
1 pc. in 1 bag	Cleanroom washed and packed	Not Available	Not Available	Not Available