


AGPLSD

AG パワーロングドリル

AG-Power Long Drills

- 生材から型鋼までの深穴加工に最適です。
- L/D20 までの深穴をノンステップで加工できます。

This drill meets non-step drilling of deep holes up to 20 times of diameter.



LIST 6540P

オーダー方法

AGPLSD 直径 × 全長

切削条件 Drilling Condition ▶▶A-229

単位 (Unit) : mm / 円 (¥)

直径 Dc	全長 L	溝長 ℓ	シリーズ Series	在庫 Stock	参考価格 Price
1.0	56	33	1	●	1,400
1.0	100	60	2	●	1,680
1.1	60	37	1	●	1,680
1.1	100	60	2	●	2,000
1.2	65	41	1	●	1,680
1.2	105	65	2	●	2,000
1.3	65	41	1	●	1,680
1.3	105	65	2	●	2,000
1.4	70	45	1	●	1,680
1.4	110	70	2	●	2,000
1.5	70	45	1	●	1,590
1.5	110	70	2	●	1,920
1.6	76	50	1	●	1,890
1.6	115	75	2	●	2,260
1.7	76	50	1	●	1,890
1.7	115	75	2	●	2,260
1.8	80	53	1	●	1,890
1.8	120	80	2	●	2,260
1.9	80	53	1	●	1,890
1.9	120	80	2	●	2,260
2.0	85	56	1	●	1,790
2.0	125	85	2	●	2,160
2.0	160	110	3	□	-
2.1	85	56	1	●	2,100
2.1	125	85	2	●	2,610
2.1	160	110	3	□	-
2.2	90	59	1	●	2,100
2.2	135	90	2	●	2,610
2.2	170	115	3	□	-
2.3	90	59	1	●	2,100
2.3	135	90	2	●	2,610
2.3	170	115	3	□	-
2.4	95	62	1	●	2,100
2.4	140	95	2	●	2,610
2.4	180	120	3	□	-
2.5	95	62	1	●	2,000
2.5	140	95	2	●	2,460
2.5	180	120	3	□	-
2.6	95	62	1	●	2,100
2.6	140	95	2	●	2,610
2.6	180	120	3	□	-
2.7	100	66	1	●	2,400
2.7	150	100	2	●	2,910
2.7	190	130	3	□	-
2.8	100	66	1	●	2,400
2.8	150	100	2	●	2,910
2.8	190	130	3	□	-
2.9	100	66	1	●	2,400
2.9	150	100	2	●	2,910
2.9	190	130	3	□	-
3.0	100	66	1	●	2,290
3.0	150	100	2	●	2,800
3.0	190	130	3	●	3,910
3.0	240	160	4	□	-
3.1	106	69	1	●	2,710
3.1	155	105	2	●	3,340
3.1	200	135	3	□	-
3.1	250	170	4	□	-
3.2	106	69	1	●	2,710
3.2	155	105	2	●	3,340

直径 Dc	全長 L	溝長 ℓ	シリーズ Series	在庫 Stock	参考価格 Price
3.2	200	135	3	□	-
3.2	250	170	4	□	-
3.3	106	69	1	●	2,710
3.3	155	105	2	●	3,340
3.3	200	135	3	□	-
3.3	250	170	4	□	-
3.4	112	73	1	●	2,710
3.4	165	115	2	●	3,340
3.4	210	145	3	□	-
3.4	265	180	4	□	-
3.5	112	73	1	●	2,580
3.5	165	115	2	●	3,150
3.5	210	145	3	●	4,360
3.5	265	180	4	□	-
3.6	112	73	1	●	2,710
3.6	165	115	2	●	3,340
3.6	210	145	3	□	-
3.6	265	180	4	□	-
3.7	112	73	1	●	2,710
3.7	165	115	2	●	3,340
3.7	210	145	3	□	-
3.7	265	180	4	□	-
3.8	119	78	1	●	3,070
3.8	175	120	2	●	3,800
3.8	220	150	3	□	-
3.8	280	190	4	□	-
3.9	119	78	1	●	3,070
3.9	175	120	2	●	3,800
3.9	220	150	3	□	-
3.9	280	190	4	□	-
4.0	119	78	1	●	2,900
4.0	175	120	2	●	3,610
4.0	220	150	3	●	4,900
4.0	280	190	4	□	-
4.1	119	78	1	●	3,070
4.1	175	120	2	●	3,800
4.1	220	150	3	□	-
4.1	280	190	4	□	-
4.2	119	78	1	●	3,070
4.2	175	120	2	●	3,800
4.2	220	150	3	□	-
4.2	280	190	4	□	-
4.3	126	82	1	●	3,460
4.3	185	125	2	●	4,290
4.3	235	160	3	□	-
4.3	295	200	4	□	-
4.4	126	82	1	●	3,460
4.4	185	125	2	●	4,290
4.4	235	160	3	□	-
4.4	295	200	4	□	-
4.5	126	82	1	●	3,280
4.5	185	125	2	●	4,090
4.5	235	160	3	●	5,490
4.5	295	200	4	□	-
4.6	126	82	1	●	3,460
4.6	185	125	2	●	4,290
4.6	235	160	3	□	-
4.6	295	200	4	□	-
4.7	126	82	1	●	3,460
4.7	185	125	2	●	4,290