


●鋼、鋳鉄の高効率加工ができます。穴深さ 5D までノンステップ加工ができます。

Able to handle drilling in steel and cast iron efficiently. Can handle non-step drilling up to 5 diameters.



LIST 6536

オーダ方法

AGPSD 直径

単位 (Unit): mm / 円 (¥)

直径 Dc	溝長 ℓ	全長 L	在庫 Stock	参考価格 Price
1.0	12	34		853
1.1	14	36		996
1.2	16	38		937
1.3				996
1.4	18	40		996
1.5				844
1.6				903
1.7	20	43		996
1.8				943
1.9	22	46		943
2.0				775
2.1	24	49		1,130
2.2				1,130
2.3	27	53		1,030
2.4				1,130
2.5	30	57		1,030
2.6				1,030
2.7				1,030
2.8	33	61		1,090
2.9				1,030
3.0				1,030
3.1				1,230
3.2	36	65		1,230
3.3				1,230
3.4				1,230
3.5	39	70		1,230
3.6				1,360
3.7				1,360
3.8				1,360
3.9				1,360
4.0	43	75	●	1,360
4.1				1,520
4.2				1,520
4.3				1,520
4.4				1,520
4.5	47	80		1,520
4.6				1,720
4.7				1,720
4.8				1,720
4.9				1,720
5.0	52	86		1,720
5.1				2,230
5.2				2,230
5.3				2,230
5.4				2,230
5.5				2,230
5.6				2,250
5.7	57	93		2,250
5.8				2,250
5.9				2,250
6.0				2,250
6.1				2,410
6.2				2,410
6.3				2,410
6.4	63	101		2,410
6.5				2,410
6.6				2,500
6.7				2,500
6.8				2,500
6.9	69	109		2,500
7.0				2,500

直径 Dc	溝長 ℓ	全長 L	在庫 Stock	参考価格 Price
7.1				2,660
7.2				2,660
7.3	69	109		2,660
7.4				2,660
7.5				2,660
7.6				2,830
7.7				2,830
7.8				2,830
7.9				2,830
8.0				2,830
8.1	75	117		3,130
8.2				3,130
8.3				3,130
8.4				3,130
8.5				3,130
8.6				3,280
8.7				3,280
8.8				3,280
8.9				3,280
9.0	81	125		3,280
9.1				3,800
9.2				3,800
9.3				3,800
9.4				3,800
9.5				3,800
9.6				4,240
9.7				4,240
9.8				4,240
9.9				4,660
10.0				4,240
10.1	87	133	●	5,230
10.2				5,000
10.3				5,000
10.4				5,230
10.5				5,000
10.6				5,820
10.7				5,820
10.8				5,820
10.9				5,820
11.0				5,290
11.1				6,420
11.2				6,420
11.3	94	142		6,420
11.4				6,420
11.5				5,850
11.6				6,980
11.7				6,980
11.8				6,980
11.9				6,980
12.0				6,340
12.1				9,030
12.2				9,030
12.3				9,030
12.4				9,030
12.5	101	151		8,230
12.6				9,750
12.7				9,750
12.8				9,750
12.9				9,750
13.0				8,790

1 本包装 (2.0mm 未満は 10 本包装)

Sold one per package (10 per package if below 2.0mm)

●は標準在庫品です。
 ●: Standard stock item.

