



Multi Auto Clamps - Guide Plate Type [Series Type]



Part name	Material	Heat Treatment	Surface Treatment
Clamp Block	S50C	HRC50 heat treatment	-
Clamp pin	SKD11	HRC60 heat treatment	-


Component Parts




	Component Parts	Quantity
(1)	Clamp Block	1
(2)	Clamp pin (input)	1
(3)	Clamp pin (output)	1

External Dimensions

Standard Type



Type with Return Mechanism




Specifications


Type	Shape	Order No.	No.	Name	Tapped Hole		Weight (kg)
					Input Side	Output Side	
Standard		109781	MT121B	Guide Plate Type	Yes	Yes	0.18
		114536	MT122B	Guide Plate Type	Yes	No	0.17
Type with Return Mechanism		114462	MR121B	Main Body (Groove Type)	Yes	Yes	0.30

Optional


Guide Plate MT12-BG



Guide Plate Mounting Dimensions



Extension Bar MT12-S



* For guide plates and extension bars, provide us with the A dimension and we will give you a separate quote.