



N-010431 T足



コード No.	L	W	A × B	C	ℓ	P	入数(1袋×数)
003	50	25	13.5 × 9	20	60	37	400(25 × 16)
004	65	25	13.5 × 9	20	60	37	350(25 × 14)
005	75	25	13.5 × 9	20	60	37	300(25 × 12)
006	100	25	13.5 × 9	20	60	37	200(25 × 8)
007	125	25	13.5 × 9	20	60	37	200(25 × 8)
008	150	25	13.5 × 9	20	60	37	200(25 × 8)
009	200	25	13.5 × 9	20	60	37	150(25 × 6)

■ネジ、ビス類で取り付ける一般的な立バンド用取り付け足です。

単位 (m/m)



t=1.5

N-010433 ステンT足 (長穴)




コード No.	L	W	A × B	ℓ	P	入数(1袋×数)
050	50	25	34.5 × 9	60	37	400(25 × 16)
060	60	25	34.5 × 9	60	37	350(25 × 14)
070	70	25	34.5 × 9	60	37	300(25 × 12)
080	80	25	34.5 × 9	60	37	300(25 × 12)
100	100	25	34.5 × 9	60	37	250(25 × 10)
120	120	25	34.5 × 9	60	37	200(25 × 8)
150	150	25	34.5 × 9	60	37	200(25 × 8)
200	200	25	34.5 × 9	60	37	150(25 × 6)
500	50	32	43 × 11	72	49	300(25 × 12)
501	60	32	43 × 11	72	49	200(25 × 8)
502	80	32	43 × 11	72	49	175(25 × 7)
503	100	32	43 × 11	72	49	150(25 × 6)
504	120	32	43 × 11	72	49	125(25 × 5)
505	150	32	43 × 11	72	49	125(25 × 5)
506	200	32	43 × 11	72	49	100(25 × 4)

■ネジ、ビス類で取り付ける一般的な立バンド用取り付け足です。

単位 (m/m)

■ SUS304



t=1.5


N-010411 長穴T足



コード No.	L	W	A × B	ℓ	P	入数(1袋×数)
251	50	25	35 × 9	60	37	400(25 × 16)
252	60	25	35 × 9	60	37	350(25 × 14)
260	70	25	35 × 9	60	37	300(25 × 12)
253	80	25	35 × 9	60	37	300(25 × 12)
254	100	25	35 × 9	60	37	250(25 × 10)
255	120	25	35 × 9	60	37	200(25 × 8)
256	150	25	35 × 9	60	37	200(25 × 8)
257	200	25	35 × 9	60	37	150(25 × 6)
321	50	32	43 × 11	72	49	300(25 × 12)
322	60	32	43 × 11	72	49	200(25 × 8)
323	80	32	43 × 11	72	49	175(25 × 7)
324	100	32	43 × 11	72	49	150(25 × 6)
325	120	32	43 × 11	72	49	130(25 × 5)
326	150	32	43 × 11	72	49	130(25 × 5)
327	200	32	43 × 11	72	49	100(25 × 4)

■ネジ、ビス類で取り付ける一般的な立バンド用取り付け足です。

単位 (m/m)



t=1.5 (2.0)

32 幅は () 内板厚になります。

N-010419 1ツ穴T足



コード No.	L	W	A × B	ℓ	P	入数(1袋×数)
030	30	25	13 × 8.5	60	38	500(25 × 20)

■吊バンドを使用する立管用T足

単位 (m/m)

N-010420 ステン1ツ穴T足





コード No.	L	W	A × B	ℓ	P	入数(1袋×数)
030	30	25	13 × 8.5	60	38	500(25 × 20)

■ステン吊バンドを使用する立管用T足

単位 (m/m)

■ SUS304



t=1.5