

Allows clamping of workpiece for processing or measurement




SBV-150T

- USE**
 - Allows clamping of workpiece for marking, processing or measurement
- MATERIAL**
 - Cast iron
- FEATURES**
 - Machine finish
 - with clamp
- SPECIFICATIONS**
 - V groove(dovetail) angle : 90°

Order No.	Model No.	Nominal Size (mm)	Groove height squareness / parallelism / perpendicularity (mm)	Length (mm)	Width (mm)	Height (mm)	Thickness (mm)	Weight
NEW 150987	SBV-100T	100	0.05	100	100	100	13	3.7kg
NEW 150988	SBV-125T	125	0.06	125	125	125	15	6.7kg
NEW 150989	SBV-150T	150	0.06	150	150	150	19	12.2kg
NEW 150990	SBV-200T	200	0.07	200	200	200	25	28.1kg


※ accuracy specified above is not guaranteed for open side

V BLOCK WITH MAGNET



MV-80G

DIMENSIONS



- USE**
 - Use as a jig to hold cylindrical workpieces for measuring or marking
- MATERIALS**
 - Cast iron/ Ground finish
- FEATURES**
 - Right angle/ Parallelism: 0.025mm/100mm
 - The magnet can be turned ON/OFF by lever operation

Units : mm

Model No.	A	B	C	D	E	F
MV-80	50	70	20	22	95	80
MV-100	50	70	20	22	95	100
MV-120	50	70	20	22	95	120

Order No.	Model No.	H × W × D (mm)	Magnetic Power** N / (lb)	Weight
NEW 151178	MV-80G	95×70× 80	140 (30)	3.3kg
NEW 151179	MV-100G	95×70×100	180 (40)	4.1kg
NEW 151180	MV-120G	95×70×120	200 (45)	4.9kg

※ Magnetic power when used with φ 20mm cylindrical workpiece