



RoHS Compliant



ERON®

No.E-404

Coupling Nuts

Material S45C Heat Treatment HRC30 ± 5 heat treatment

Surface Treatment Blackened



Specifications

Order No.	No.	Screw Diameter (Coarse Thread)	A	B	Weight (g)	
01112	CNM0008	M8×1.25	13	22	17	
02675	CNM0010	M10×1.5	17	25	40	
02676	CNM0012	M12×1.75	19	29	48	
02677	CNM0014	M14×2	22	32	75	
02678	CNM0016	M16×2	24	36	90	
02679	CNM0018	M18×2.5	27	41	130	
02680	CNM0020	M20×2.5	30	44	175	
02681	CNM0022	M22×2.5	32	48	210	
02682	CNM0024	M24×3	36	57	340	
95975	CNM0030	M30	46	70	693	

Base Elements

Clamp Units

Clamping Parts

Machine Vises

Drilling Vises

Vibration Isolation

Surface Plates and Measurement Instruments

Index



RoHS Compliant

ERON®



No.E-404

Coupling Nuts (Type Long)


Material S45C Heat Treatment HRC30 ± 5 heat treatment

Surface Treatment Blackened

- Does not come loose easily thanks to the long screw part.
- The B dimension is set to 3 times the screw diameter.



Usage Examples



Specifications

Order No.	No.	Screw Diameter (Coarse Thread)	A	B	Weight (g)	
51944	CNL016	M16×2	24	48	120	
51945	CNL020	M20×2.5	30	60	240	
51946	CNL022	M22×2.5	32	66	280	
51947	CNL024	M24×3	36	72	400	