

Size Chart

No.	A	B	C	D	E	F	G
P150	38	38	25	47	108	22	25.5
P250	62	64	38	67	158	29	37
P350	75	79	45	76	186	31	38.5
P400	101.5	104	45	83	238	38	48
P300	81	84	38	66	183	28	37.5
P770	94	105	42.5	66	273	23.5	24

No.	H	I	J	K	O	P	R
P150	46	5	W3/8 16 threads per inch	Ø12	-	-	-
P250	97	8	W1/2 12 threads per inch	Ø19	-	-	-
P350	114	8	TW16 8 threads per inch	Hex 22	-	-	-
P400	114	8	TW16 8 threads per inch	Hex 22	-	-	-
P300	114	8	TW16 8 threads per inch	Hex 22	101	66.5	17
P770	114	8	TW16 8 threads per inch	Hex 22	127	127	13

Specifications

Order No.	No.	Jaw Width	Jaw Depth	Jaw Opening	Weight (kg)
00079	P150	38	25	38	0.8
00493	P250	62	38	64	2.6
00494	P350	75	45	79	4.4
00495	P400	101.5	45	104	7.7
00499	P300	81	38	84	3.9
00500	P770	94	42.5	105	5.2

Accessories

Jaw plates (2 pieces per set)

Compatible Models	Order No.	No.
P150,P150A	30959	P150-JA
P250,P250A,P250AS	30960	P250-JA
P350,P350A,P350AS	30962	P350-JA
P400,P400A,P400AS	30963	P400-JA
P300	30961	P300-JA

Back plate

Compatible Models	Order No.	No.
P150,P150A	43915	P150-BP
P250,P250A,P250AS,P300	43916	P250-BP
P350,P350A,P350AS	43917	P350-BP
P400,P400A,P400AS,P770	43918	P400-BP

Spindle

Compatible Models	Order No.	No.
P150	43909	P150 -SP
P150A	43910	P150A-SP
P250	43911	P250 -SP
P250A,P250AS	43912	P250A-SP
P350	46805	P350 -SP
P350A,P350AS,P400,P770	43913	P400 -SP
P400A,P400AS	43914	P400A-SP

Base Elements

Clamp Units

Clamping Parts

Machine Vises

Drilling Vises

Vibration
IsolationSurface Plates and
Measurement Instruments

Index