

PRECISION BRUSHLESS MICRO-GRINDER

Expert 500 Sets

With Motor ON/OFF Switch

- Speed Range : 1,000~50,000 min⁻¹
- Microprocessor controlled for optimal motor control
- Hand Switch [NAKANISHI Smart Switch]
- Memory Speed Function [FiXspeed®]

**High Power &
High Torque !!**



Expert 500 Standard Set



1,000~50,000 min⁻¹ **140w**

- High Power System.
<Max. Output 140W>

Code No.	9881 (120V)
	9882 (230V)
Model	ES50C-HR

※ Please check the power source plug type (p.4-6).

Standard Equipment

- Controller (NE96) : 1 pc.
- Compact Motor Handpiece (ENK50C-HR) : 1 pc.

Standard Accessories

- Collet ø3.0 mm (CHH-3.0), ø2.35 mm (CHH-2.35)
- Handpiece Holder : 1 pc. • Handpiece Stand : 1 pc.
- Wrench (7 x 5.1) : 1 pc. • Pin Wrench (K-233) : 1 pc.
- L Shaped Wrench (9) : 1 pc.

Expert 500 Torque Set



1,000~50,000 min⁻¹ **200w**

- Highest Power in its Class.
<Max. Output 200W>

Code No.	9883 (120V)
	9884 (230V)
Model	ES50T-HR

※ Please check the power source plug type (p.4-6).

Standard Equipment

- Controller (NE96) : 1 pc.
- Torque Motor Handpiece (ENK50T-HR) : 1 pc.

Standard Accessories

- Collet ø3.0 mm (CHH-3.0), ø2.35 mm (CHH-2.35)
- Handpiece Holder : 1 pc. • Handpiece Stand : 1 pc.
- Wrench (7 x 5.1) : 1 pc. • Pin Wrench (K-233) : 1 pc.
- L Shaped Wrench (9) : 1 pc.

CAUTION

Electric System

Air System

Ultrasonic

General Parts

Exclusive Tools