


円筒ころ軸受

内径：17～30mm



1N=0.102kgf

主要寸法 (mm)							呼び番号						基本 静定格 荷重 Cr (N)	基本 動定格 荷重 Cor (N)	許容回転速度 (min ⁻¹) ⁽¹⁾	
d	D	B	Ew	Fw	r (最小)	r1 (最小)	NU	NJ	NUP	N	NF	NP	グリース 潤滑	油潤滑		
17	40	12	33.9	22.9	0.6	0.3	NU 203	NJ	NUP	N	NF	NP	12600	7950	16000	19000
20	47	14	40	27	1	0.6	NU 204	NJ	NUP	N	NF	NP	15400	12700	15000	18000
	47	14	—	26.5	1	0.6	NU 204 E	NJ	NUP	—	—	—	25700	22600	13000	16000
	47	18	—	27	1	0.6	NU 2204	NJ	NUP	—	—	—	20700	18400	14000	17000
	47	18	—	26.5	1	0.6	NU 2204 E	NJ	NUP	—	—	—	30500	28300	13000	16000
	52	15	44.5	28.5	1.1	0.6	NU 304	NJ	NUP	N	NF	NP	21400	17300	12000	15000
	52	15	—	27.5	1.1	0.6	NU 304 EG	NJ	NUP	—	—	—	31500	26900	12000	15000
	52	21	—	28.5	1.1	0.6	NU 2304	NJ	NUP	—	—	—	30500	27200	11000	14000
52	21	—	27.5	1.1	0.6	NU 2304 E	NJ	NUP	—	—	—	42000	39000	11000	14000	
25	47	12	41.5	30.5	0.6	0.3	NU 1005	—	—	N	—	—	14300	13100	15000	18000
	52	15	45	32	1	0.6	NU 205	NJ	NUP	N	NF	NP	17700	15700	13000	16000
	52	15	—	31.5	1	0.6	NU 205 EG	NJ	NUP	—	—	—	29300	27700	12000	14000
	52	18	—	32	1	0.6	NU 2205	NJ	NUP	—	—	—	24300	23500	12000	14000
	52	18	—	31.5	1	0.6	NU 2205 EG	NJ	NUP	—	—	—	35000	34500	12000	14000
	62	17	53	35	1.1	1.1	NU 305	NJ	NUP	N	NF	NP	29300	25200	10000	13000
	62	17	—	34	1.1	1.1	NU 305 EG	NJ	NUP	—	—	—	41500	37500	10000	12000
	62	24	—	35	1.1	1.1	NU 2305	NJ	NUP	—	—	—	42500	41000	9300	11000
62	24	—	34	1.1	1.1	NU 2305 E	NJ	NUP	—	—	—	57000	56000	9000	11000	
80	21	62.8	38.8	1.5	1.5	NU 405	NJ	NUP	N	NF	NP	46500	40000	9000	11000	
30	55	13	48.5	36.5	1	0.6	NU 1006	—	—	N	—	—	19700	19600	12000	15000
	62	16	53.5	38.5	1	0.6	NU 206	NJ	NUP	N	NF	NP	23500	21500	11000	13000
	62	16	—	37.5	1	0.6	NU 206 EG	NJ	NUP	—	—	—	39000	37500	9500	12000
	62	20	—	38.5	1	0.6	NU 2206	NJ	NUP	—	—	—	33000	33000	10000	12000
	62	20	—	37.5	1	0.6	NU 2206 EG	NJ	NUP	—	—	—	49000	50000	9500	12000
	72	19	62	42	1.1	1.1	NU 306	NJ	NUP	N	NF	NP	38500	35000	8500	11000
	72	19	—	40.5	1.1	1.1	NU 306 EG	NJ	NUP	—	—	—	53000	50000	8500	10000
	72	27	—	42	1.1	1.1	NU 2306	NJ	NUP	—	—	—	51500	51000	8200	9800
	72	27	—	40.5	1.1	1.1	NU 2306 E	NJ	NUP	—	—	—	74500	77500	8000	9500
	90	23	73	45	1.5	1.5	NU 406	NJ	NUP	N	NF	NP	62500	55000	7500	9500

注(1) 許容回転速度は、もみぬき保持器の場合を示す。プレス保持器の場合は上記の80%まで許容する。