

トルネード PM

TORNADO PM

●中実材から異形材まで幅広い形状に適用。

Applicable from solid material to variant material.



オーダー方法

商品記号

商品記号 CODE	全長 OAL	幅 Width	厚さ Thickness	刃数 TPI	在庫 Stock	参考価格 Price
※ BPV27504-6	2750	27	0.95	4/6	●	7,200
※ BPV27505-7	2750	27	0.95	5/7	●	7,200
※ BPV27506-10	2750	27	0.95	6/10	●	7,200
※ BPV27508-12	2750	27	0.95	8/12	●	7,200
BPV35052-3	3505	27	0.95	2/3	●	9,200
BPV35053-4	3505	27	0.95	3/4	●	9,200
BPV35054-6	3505	27	0.95	4/6	●	9,200
BP35053	3505	27	0.95	3	●	9,200
BP35054	3505	27	0.95	4	●	9,200
BPV36602-3	3660	27	0.95	2/3	●	9,200
BPV36603-4	3660	27	0.95	3/4	●	9,200
BPV36604-6	3660	27	0.95	4/6	●	9,200
BP36603	3660	27	0.95	3	●	9,200
BP36604	3660	27	0.95	4	●	9,200
※ BPV37504-6	3750	27	0.95	4/6	●	9,200
※ BPV37505-7	3750	27	0.95	5/7	●	9,200
※ BPV37506-10	3750	27	0.95	6/10	●	9,200
※ BPV37508-12	3750	27	0.95	8/12	●	9,200
BPWV35052-3	3505	34	1.07	2/3	●	11,400
BPWV35053-4	3505	34	1.07	3/4	●	11,400
BPWV35054-6	3505	34	1.07	4/6	●	11,400
BPWV36604-6	3660	34	1.07	4/6	●	11,400
BPWV41152-3	4115	34	1.07	2/3	●	12,000
BPWV41153-4	4115	34	1.07	3/4	●	12,000
BPWV41154-6	4115	34	1.07	4/6	●	12,000
BPW41152	4115	34	1.07	2	●	12,000
BPW41153	4115	34	1.07	3	●	12,000
BPW41154	4115	34	1.07	4	●	12,000
BPWV42102-3	4210	34	1.07	2/3	●	12,000
BPWV42103-4	4210	34	1.07	3/4	●	12,000
BPWV42104-6	4210	34	1.07	4/6	●	12,000
BPWV45702-3	4570	34	1.07	2/3	●	12,600
BPWV45703-4	4570	34	1.07	3/4	●	12,600
BPWV45704-6	4570	34	1.07	4/6	●	12,600
BPW45702	4570	34	1.07	2	●	12,600
BPW45703	4570	34	1.07	3	●	12,600
BPW45704	4570	34	1.07	4	●	12,600
BPWV48803-4	4880	34	1.07	3/4	●	12,600
BPQV45702-3	4570	41	1.3	2/3	●	16,600
BPQV46702-3	4670	41	1.3	2/3	●	16,600
BPQV46703-4	4670	41	1.3	3/4	●	16,600
BPQV46704-6	4670	41	1.3	4/6	●	16,600
BPQV47202-3	4720	41	1.3	2/3	●	16,600
BPQV47203-4	4720	41	1.3	3/4	●	16,600
BPQV48802-3	4880	41	1.3	2/3	●	16,600
BPQV48803-4	4880	41	1.3	3/4	●	16,600
BPQ48802	4880	41	1.3	2	●	16,600
BPQ48803	4880	41	1.3	3	●	16,600
BPQV50402-3	5040	41	1.3	2/3	●	18,900
BPQV50403-4	5040	41	1.3	3/4	●	18,900
BPQV50404-6	5040	41	1.3	4/6	●	18,900
BPQV53002-3	5300	41	1.3	2/3	●	18,900
BPQV53003-4	5300	41	1.3	3/4	●	18,900
BPQV53004-6	5300	41	1.3	4/6	●	18,900

※印は、ロータリーマシン用メタルバンドソー「トルネードPM」と同一品です。

切削条件 Cutting Condition ▶▶ D-12

単位 (Unit) : mm

商品記号 CODE	全長 OAL	幅 Width	厚さ Thickness	刃数 TPI	在庫 Stock	参考価格 Price
BPQ53002	5300	41	1.3	2	●	18,900
BPQ53003	5300	41	1.3	3	●	18,900
BPQV54502-3	5450	41	1.3	2/3	●	18,900
BPQV54503-4	5450	41	1.3	3/4	●	18,900
BPQV54504-6	5450	41	1.3	4/6	●	18,900

オーダー方法

タイプ 全長 幅 刃数

単位 (Unit) : mm

タイプ Type	全長 OAL	幅 Width	厚さ Thickness	在庫 Stock								
				刃数 TPI								
				0.75/1	1/1.5	1/2	1.5/2	2/3	3/4	4/6	5/7	6/10
BPV	ご指定ください	27	0.95					△	△	△	△	△
BPWV		27	1.07					△	△	△		
BPWV		34	1.07					△	△	△		
BPQV	41	1.3						△	△	△		
	54	1.3						△	△	△		
BPHV	54	1.6		△	△	△	△	△	△			
	67	1.6		△	△	△	△	△	△			
	80	1.6	△									

オーダー方法

タイプ 全長 幅 刃数

単位 (Unit) : mm

タイプ Type	全長 OAL	幅 Width	厚さ Thickness	在庫 Stock				
				刃数 TPI				
				2	3	4	6	
BP	ご指定ください	27	0.95			△	△	△
BPW		34	1.07			△	△	△
BPQ		41	1.3			△	△	△

在庫表示

●印：標準在庫品です。
△印：受注生産品です。
無印：製作いたしません。

Stocking marks

●：Stocked items.
△：Manufactured upon request.
No mark：Not manufactured.

カットオフマシン用メタルバンドソーの梱包数量
Packed Quantity

幅 Width	全長 OAL	数量 Pcs.
27	2750	5
27	3505 ~ 3660	5
27	3750	5
34	3660 ~ 5334	5
41	4570 ~ 6095	5
41	6650	2
54	6500 ~ 8300	2
67	8800 ~ 13365	1