


GOH

G オイルホールドリル

G Oil-Hole Drills

- 汎用のコーティングオイルホールドリルです。
- サイドロックシャンクを採用しています。

This side lock shank drill is general coated oil-hole drills.



LIST 6558P

オーダー方法

GOH 直径 *印商品のオーダー方法 GOH 直径 × シャンク径

切削条件 Drilling Condition ▶▶▶A-236

単位 (Unit) : mm / 円 (¥)

直径 Dc	溝長 l	全長 L	シャンク径 Ds	シャンク長 ls	在庫 Stock	参考価格 Price
8.0	33	83	16	48	●	32,100
8.1	33	83	16	48	□	-
8.2	33	83	16	48	□	-
8.3	33	83	16	48	□	-
8.4	33	83	16	48	□	-
8.5	33	83	16	48	●	32,100
8.6	38	88	16	48	□	-
8.7	38	88	16	48	□	-
8.8	38	88	16	48	□	-
8.9	38	88	16	48	□	-
9.0	38	88	16	48	●	32,100
9.1	38	88	16	48	□	-
9.2	38	88	16	48	□	-
9.3	38	88	16	48	□	-
9.4	38	88	16	48	□	-
9.5	38	88	16	48	●	32,100
9.6	43	93	16	48	□	-
9.7	43	93	16	48	□	-
9.8	43	93	16	48	□	-
9.9	43	93	16	48	□	-
10.0	43	93	16	48	●	25,700
10.1	43	93	16	48	□	-
10.2	43	93	16	48	□	-
10.3	43	93	16	48	□	-
10.4	43	93	16	48	□	-
10.5	43	93	16	48	●	25,700
10.6	48	98	16	48	□	-
10.7	48	98	16	48	□	-
10.8	48	98	16	48	□	-
10.9	48	98	16	48	□	-
11.0	48	98	16	48	●	26,100
11.1	48	98	16	48	□	-
11.2	48	98	16	48	□	-
11.3	48	98	16	48	□	-
11.4	48	98	16	48	□	-
11.5	48	98	16	48	●	26,100
11.6	53	103	16	48	□	-
11.7	53	103	16	48	□	-
11.8	53	103	16	48	□	-
11.9	53	103	16	48	□	-
12.0	53	103	16	48	●	26,300
12.1	53	103	16	48	□	-
12.2	53	103	16	48	□	-
12.3	53	103	16	48	□	-
12.4	53	103	16	48	□	-
12.5	53	103	16	48	●	26,300
12.6	58	108	16	48	□	-
12.7	58	108	16	48	□	-
12.8	58	108	16	48	□	-
12.9	58	108	16	48	□	-
13.0	58	108	16	48	●	26,600
13.1	58	108	16	48	□	-
13.2	58	108	16	48	□	-
13.3	58	108	16	48	□	-
13.4	58	108	16	48	□	-
13.5	58	108	16	48	●	26,600
13.6	63	113	16	48	□	-
13.7	63	113	16	48	□	-
13.8	63	113	16	48	□	-
13.9	63	113	16	48	□	-

直径 Dc	溝長 l	全長 L	シャンク径 Ds	シャンク長 ls	在庫 Stock	参考価格 Price
14.0	63	113	16	48	●	27,000
14.1	63	113	16	48	□	-
14.2	63	113	16	48	□	-
14.3	63	113	16	48	□	-
14.4	63	113	16	48	□	-
14.5	63	113	16	48	●	27,000
14.6	70	125	20	50	□	-
14.7	70	125	20	50	□	-
14.8	70	125	20	50	□	-
14.9	70	125	20	50	□	-
15.0	70	125	20	50	●	27,300
15.1	70	125	20	50	□	-
15.2	70	125	20	50	□	-
15.3	70	125	20	50	□	-
15.4	70	125	20	50	□	-
15.5	70	125	20	50	●	27,300
15.6	75	130	20	50	□	-
15.7	75	130	20	50	□	-
15.8	75	130	20	50	□	-
15.9	75	130	20	50	□	-
16.0	75	130	20	50	●	27,800
16.1	75	130	20	50	□	-
16.2	75	130	20	50	□	-
16.3	75	130	20	50	□	-
16.4	75	130	20	50	□	-
16.5	75	130	20	50	●	27,800
16.6	80	135	20	50	□	-
16.7	80	135	20	50	□	-
16.8	80	135	20	50	□	-
16.9	80	135	20	50	□	-
17.0	80	135	20	50	●	28,300
17.1	80	135	20	50	□	-
17.2	80	135	20	50	□	-
17.3	80	135	20	50	□	-
17.4	80	135	20	50	□	-
17.5	80	135	20	50	●	28,300
17.6	85	140	20	50	□	-
17.7	85	140	20	50	□	-
17.8	85	140	20	50	□	-
17.9	85	140	20	50	□	-
18.0	85	140	20	50	●	28,800
18.1	85	140	20	50	□	-
18.2	85	140	20	50	□	-
18.3	85	140	20	50	□	-
18.4	85	140	20	50	□	-
18.5	85	140	20	50	●	28,800
18.6	95	156	25	56	□	-
18.7	95	156	25	56	□	-
18.8	95	156	25	56	□	-
18.9	95	156	25	56	□	-
19.0	95	156	25	56	●	29,400
19.1	95	156	25	56	□	-
19.2	95	156	25	56	□	-
19.3	95	156	25	56	□	-
19.4	95	156	25	56	□	-
19.5	95	156	25	56	●	29,400
19.6	95	156	25	56	□	-
19.7	95	156	25	56	□	-
19.8	95	156	25	56	□	-
19.9	95	156	25	56	□	-