


# クイックシールシリーズ インサートタイプ(黄銅仕様)

## ティー

### ●ミリサイズ(グループ4)



品番	適用チューブ外径X内径(mm)	Tねじサイズ(R)	L1(mm)	L2(mm)	L3(mm)	L4(mm)	L5(mm)	A(mm)	S(mm)	Fチューブ挿入長さ(mm)	H1二面幅(mm)	H2二面幅(mm)	d1(mm)	d2最小内径(mm)	有効断面積(mm <sup>2</sup> )	質量(g)
T4N4X2-PT1/8	4X2	R1/8	20.5	18.5	24.3	41.0	11.0	4.7	15	10.0	10.0	5.0	0.9	0.5	25.0	
T4N4X2.5-PT1/8	4X2.5	R1/8	20.5	18.5	24.3	41.0	11.0	4.7	15	10.0	10.0	5.0	1.3	1.5	25.0	
T4N4X3-PT1/8	4X3	R1/8	20.5	18.5	24.3	41.0	11.0	4.7	15	10.0	10.0	5.0	2.0	2.5	25.0	
T4N6X4-PT1/8	6X4	R1/8	20.5	18.5	25.4	41.0	11.0	4.6	15	10.0	12.0	5.0	2.7	4.5	30.0	
T4N6X4-PT1/4	6X4	R1/4	23.0	22.0	28.9	46.0	12.0	4.6	15	12.0	12.0	7.0	2.7	4.5	43.0	
T4N6X4.5-PT1/8	6X4.5	R1/8	20.5	18.5	25.4	41.0	11.0	4.6	15	10.0	12.0	5.0	3.2	7.0	31.0	
T4N6X4.5-PT1/4	6X4.5	R1/4	23.0	22.0	28.9	46.0	12.0	4.6	15	12.0	12.0	7.0	3.2	7.0	43.0	
T4N8X5-PT1/8	8X5	R1/8	22.9	21.0	29.1	45.8	11.0	4.6	16	12.0	14.0	5.0	3.7	9.0	43.0	
T4N8X5-PT1/4	8X5	R1/4	22.9	22.0	30.1	45.8	12.0	4.6	16	12.0	14.0	7.0	3.7	9.0	45.0	
T4N8X6-PT1/8	8X6	R1/8	22.9	21.0	29.1	45.8	11.0	4.6	16	12.0	14.0	5.0	4.7	14.0	42.0	
T4N8X6-PT1/4	8X6	R1/4	22.9	22.0	30.1	45.8	12.0	4.6	16	12.0	14.0	7.0	4.7	15.0	44.0	
T4N8X6-PT3/8	8X6	R3/8	22.9	26.0	34.1	45.8	13.0	4.6	16	14.0	14.0	9.0	4.7	15.0	58.0	
T4N10X6.5-PT1/4	10X6.5	R1/4	27.1	25.0	34.8	54.2	12.0	4.2	17	14.0	17.0	7.0	5.2	18.0	73.0	
T4N10X6.5-PT3/8	10X6.5	R3/8	28.1	26.0	35.8	56.2	13.0	4.2	17	14.0	17.0	9.0	5.2	18.0	78.0	
T4N10X7.5-PT1/4	10X7.5	R1/4	27.1	25.0	34.8	54.2	12.0	4.2	17	14.0	17.0	7.0	6.2	24.0	70.0	
T4N10X7.5-PT3/8	10X7.5	R3/8	27.1	26.0	35.8	54.2	13.0	4.2	17	14.0	17.0	9.0	6.2	26.0	76.0	
T4N10X8-PT1/2	10X8	R1/2	27.1	33.0	43.4	54.2	18.0	4.2	17	18.0	17.0	12.0	6.2	26.0	110.0	
T4N10X8-PT1/4	10X8	R1/4	27.1	25.0	34.8	54.2	12.0	4.2	17	14.0	17.0	7.0	6.7	25.0	69.0	
T4N10X8-PT3/8	10X8	R3/8	27.1	26.0	35.8	54.2	13.0	4.2	17	14.0	17.0	9.0	6.7	25.0	75.0	
T4N10X8-PT1/2	10X8	R1/2	27.1	33.0	43.4	54.2	18.0	4.2	17	18.0	17.0	12.0	6.7	30.0	109.0	
T4N12X8-PT3/8	12X8	R3/8	27.6	25.0	36.0	55.3	13.0	4.8	18	14.0	19.0	9.0	6.6	25.0	82.0	
T4N12X8-PT1/2	12X8	R1/2	30.6	33.0	44.0	61.3	18.0	4.8	18	18.0	19.0	12.0	6.6	30.0	128.0	
T4N12X9-PT1/4	12X9	R1/4	27.6	25.0	36.0	55.3	12.0	4.8	18	14.0	19.0	7.0	7.6	33.0	75.0	
T4N12X9-PT3/8	12X9	R3/8	27.6	26.0	37.0	55.3	13.0	4.8	18	14.0	19.0	9.0	7.6	33.0	82.0	
T4N12X9-PT1/2	12X9	R1/2	30.6	33.0	44.0	61.3	18.0	4.8	18	18.0	19.0	12.0	7.6	33.0	128.0	
T4N16X13-PT1/2	16X13	R1/2	36.7	33.0	48.6	73.4	18.0	5.1	23	23.0	27.0	12.0	11.0	72.0	165.0	

※受注生産品

### ●インチサイズ(グループ1)

品番	適用チューブ外径(inch)	Tねじサイズ(R)	L1(mm)	L2(mm)	L3(mm)	L4(mm)	A(mm)	S(mm)	Fチューブ挿入長さ(mm)	H1二面幅(mm)	H2二面幅(mm)	d1(mm)	d2最小内径(mm)	有効断面積(mm <sup>2</sup> )	質量(g)
T1N1/8-PT1/8	1/8	R1/8	20.5	18.5	24.3	41.1	11.0	4.6	15	10.0	8.0	5.0	1.4	1.5	21.0
T1N3/16-PT1/8	3/16	R1/8	20.6	18.5	24.3	41.1	11.0	4.6	15	10.0	10.0	5.0	2.4	4.0	26.0
T1N1/4-PT1/8	1/4	R1/8	20.5	18.5	25.4	41.1	11.0	4.6	15	10.0	12.0	5.0	3.4	8.0	29.0
T1N1/4-PT1/4	1/4	R1/4	23.0	22.0	28.9	46.1	12.0	4.6	15	12.0	12.0	7.0	3.4	8.0	42.0
T1N5/16-PT1/8	5/16	R1/8	22.8	21.0	29.1	45.7	11.0	4.6	16	12.0	14.0	5.0	4.7	15.0	42.0
T1N5/16-PT1/4	5/16	R1/4	22.8	22.0	30.1	45.7	12.0	4.6	16	12.0	14.0	7.0	4.7	15.0	45.0
T1N5/16-PT3/8	5/16	R3/8	25.8	26.0	34.1	51.7	13.0	4.6	16	14.0	14.0	9.0	4.7	15.0	66.0
T1N3/8-PT1/4	3/8	R1/4	23.7	22.0	31.8	47.4	12.0	4.6	17	12.0	17.0	7.0	5.7	19.0	55.0
T1N3/8-PT3/8	3/8	R3/8	26.7	26.0	35.8	53.4	13.0	4.6	17	14.0	17.0	9.0	5.7	19.0	77.0
T1N3/8-PT1/2	3/8	R1/2	29.7	33.0	43.4	59.4	18.0	4.6	17	18.0	17.0	12.0	5.7	22.5	122.0
T1N1/2-PT3/8	1/2	R3/8	27.8	26.0	37.0	55.6	13.0	4.6	18	14.0	19.0	9.0	8.2	32.0	79.0
T1N1/2-PT1/2	1/2	R1/2	30.8	33.0	44.0	61.6	18.0	4.6	18	18.0	19.0	12.0	8.2	32.0	119.0
T1N5/8-PT3/8	5/8	R3/8	36.7	28.0	43.6	73.3	13.0	5.1	23	18.0	27.0	9.0	9.3	48.0	130.0
T1N5/8-PT1/2	5/8	R1/2	36.7	33.0	48.6	73.3	18.0	5.1	23	18.0	27.0	12.0	9.3	53.0	172.0

### ●インチサイズ(グループ2)

品番	適用チューブ外径(inch)	Tねじサイズ(R)	L1(mm)	L2(mm)	L3(mm)	L4(mm)	A(mm)	S(mm)	Fチューブ挿入長さ(mm)	H1二面幅(mm)	H2二面幅(mm)	d1(mm)	d2最小内径(mm)	有効断面積(mm <sup>2</sup> )	質量(g)
T2N1/8-PT1/8	1/8	R1/8	20.5	18.5	24.3	41.1	11.0	4.6	21	10.0	8.0	5.0	3.0	1.5	20.5
T2N3/16-PT1/8	3/16	R1/8	20.6	18.5	24.3	41.1	11.0	4.6	15	10.0	10.0	5.0	1.4	1.5	25.0
T2N1/4-PT1/8	1/4	R1/8	20.5	18.5	25.4	41.1	11.0	4.6	15	10.0	12.0	5.0	2.2	3.5	30.0
T2N1/4-PT1/4	1/4	R1/4	23.0	22.0	28.9	46.1	12.0	4.6	15	12.0	12.0	7.0	2.2	3.5	43.0
T2N5/16-PT1/8	5/16	R1/8	22.8	21.0	29.1	45.7	11.0	4.6	16	12.0	14.0	5.0	2.9	5.0	45.0
T2N5/16-PT1/4	5/16	R1/4	22.8	22.0	30.1	45.7	12.0	4.6	16	12.0	14.0	7.0	2.9	5.0	43.0
T2N3/8-PT1/4	3/8	R1/4	23.7	22.0	31.8	47.4	12.0	4.6	17	12.0	17.0	7.0	3.5	7.5	57.0
T2N3/8-PT3/8	3/8	R3/8	26.7	26.0	35.8	53.4	13.0	4.6	17	14.0	17.0	9.0	3.5	7.5	78.0
T2N1/2-PT3/8	1/2	R3/8	27.8	26.0	37.0	55.6	13.0	4.6	18	14.0	19.0	9.0	5.2	18.0	80.0

☆T2N1/8-PT1/8はインサートレスタイプになります。

チューブ

クリートン  
チューブ

加工チューブ

プッシュオン  
継手

クイックシール  
継手

クリートン継手  
ケミファイット

竹のこ継手

制御切替・着脱  
シリーズ

治具・工具  
付属品

技術資料

参考資料