


4AGEL

AGミル 4枚刃ロング

AG-mill Four Flutes Long

●幅の広い側面や深い位置の側面加工に適しています。

This end mill is suitable for high-feed side milling of workpiece material from Steels and Stainless Steels to Aluminum.



LIST 6498

オーダ方法

切削条件 Milling Condition **B-269**

4AGEL 外径

単位 (Unit) : mm / 円 (¥)

外径 Dc	刃長 ℓ	全長 L	シャンク径 Ds	在庫 Stock	参考価格 Price
3	15	60	6	●	3,240
4	20	60	8	●	3,240
5	25	65	8	●	3,240
6	25	65	8	●	3,240
7	35	80	10	●	3,740
8	35	80	10	●	3,740
9	45	95	10	●	4,180
10	45	95	10	●	4,180
11	55	105	12	●	5,150
12	55	105	12	●	5,150
13	55	110	16	●	6,640
14	55	110	16	●	6,640
15	65	120	16	●	7,340
16	65	120	16	●	8,190
17	65	130	20	●	9,980
18	65	130	20	●	9,980
19	75	140	20	●	11,600
20	75	140	20	●	11,600
21	75	140	20	●	14,600
22	75	140	20	●	14,600
23	90	160	25	●	18,100
24	90	160	25	●	18,100
25	90	160	25	●	18,100
26	90	160	25	●	19,900
27	90	160	25	●	23,700
28	90	160	25	●	23,700
29	90	160	25	●	28,600
30	90	160	25	●	28,600
31	105	190	32	●	34,900
32	105	190	32	●	34,900
33	105	190	32	●	43,500
34	105	190	32	●	43,500
35	105	190	32	●	45,900
36	105	190	32	●	45,900
37	125	210	32	●	51,200
38	125	210	32	●	51,200
39	125	210	32	●	60,200
40	125	210	32	●	60,200

オーダ方法

4AGELPT 外径

単位 (Unit) : mm / 円 (¥)

外径 Dc	刃長 ℓ	全長 L	シャンク径 Ds	在庫 Stock	参考価格 Price
10	45	95	10	●	4,180
12	55	105	12	●	5,150
16	65	120	16	●	8,190
20	75	140	20	●	11,600
25	90	160	25	●	18,100


SL4SGE

SG-FAX エンドミル ロング 4枚刃

SG-FAX End Mills Long Four Flutes

●幅の広い側面や深い位置の側面加工に適しています。

This end mill is suitable for high-feed side milling of workpiece material from Steels and Stainless Steels to Aluminum.



LIST 7466P

オーダ方法

切削条件 Milling Condition **B-271**

SL4SGE 外径

単位 (Unit) : mm / 円 (¥)

外径 Dc	刃長 ℓ	全長 L	シャンク径 Ds	在庫 Stock	参考価格 Price
3	15	65	6	●	4,700
4	20	70	8	●	4,700
5	25	75	8	●	4,700
6	25	75	8	●	4,700
7	35	95	10	●	5,440
8	35	95	10	●	5,440
9	45	110	10	●	6,090
10	45	110	12	●	6,090
11	55	120	12	●	7,450
12	55	120	12	●	7,450
13	55	125	16	●	10,300
14	55	125	16	●	10,300
15	65	135	16	●	11,500
16	65	135	16	●	12,800
17	65	145	20	●	15,500
18	65	145	20	●	15,500
19	75	155	20	●	18,100
20	75	155	20	●	18,100
21	75	165	20	●	22,700
22	75	165	20	●	22,700
23	90	180	25	●	28,100
24	90	180	25	●	28,100
25	90	180	25	●	28,100
26	90	180	25	●	30,800
27	90	180	25	●	36,300
28	90	180	25	●	36,300
29	90	180	25	●	44,000
30	90	180	25	●	44,000

外径 (mm) Dc		許容差 (mm) Tolerance
を越え Above	以下 Up to	
	10	+ 0.020 ~ 0
10		+ 0.025 ~ 0

4AGELPT

外径 (mm) Dc		許容差 (mm) Tolerance	
を越え Above	以下 Up to	4AGEL	4AGELPT
	10	0 ~ +0.020	+ 0.020 ~ 0
10	30	0 ~ -0.025	+ 0.025 ~ 0
30		0 ~ -0.030	

4AGEL と 4AGELPT は外径許容差が異なります。