



プレーンクランプ

PLAIN CLAMP



30P-250
30P-315
販売は1ヶ単位

- 材質 S45C
 - 硬度 HRC35°
 - 仕上 黒染
- (2ヶ1組)



(寸法表) ※1ヶ単位 長さ(mm) 質量約(kg)

No.	A	B	C	D	E	F	使用 ボルト	質量 1ヶ単位
30P-250	40	80	250	34	62	66	M 30	5.0
30P-315	50	80	315	34	62	96	M 30	6.3

(寸法表) ※2ヶ1組 単位 長さ(mm) 質量約(kg)


No.	A	B	C	D	E	F	使用 ボルト	質量 (1組)
25P-38	12	25	63		18	19	M 8	0.12
40P-38	16	25	100	10.6	27	37	M 10	0.23
60P-38	19	32	150		30	50		0.47
25P-12	12	25	63		20	14	M 12	0.12
40P-12	19	32	100	14.2	29	34	M 14	0.38
60P-12	22	32	150		32	50		0.68
25P-58	16	32	63		22	12		0.17
40P-58	19	38	100	17.0	31	26	M 16	0.42
60P-58	22	38	150		40	47		0.72
80P-58	25	50	200		55	65		1.41
40P-34	19	38	100		33	27		0.38
60P-34	25	38	150	21.0	43	44	M 18	0.76
80P-34	25	50	200		55	65	M 20	1.52
10P-34	38	50	250		60	64		2.64
60P-10	30		150		43	38		1.29
80P-10	32	50	200	26.0	53	57	M 22	2.00
10P-10	38		250		60	64	M 24	2.95
12P-10	38		300		60	64		3.50

ステップクランプ

STEP CLAMP



- 材質 S45C
 - 硬度 HRC35°
 - 仕上 黒染
- (2ヶ1組)



このクランプはステップブロックと関連したクランプで
ラックはどのブロックとも噛合します。

(寸法表) 単位 長さ(mm) 質量約(kg)


No.	A	B	C	D	E	F	使用 ボルト	質量 (1組)
25S-38	12	25	63		18	19	M 8	0.12
40S-38	16	25	100	10.6	27	37	M 10	0.23
60S-38	19	32	150		30	50		0.47
25S-12	12	25	63		20	14	M 12	0.12
40S-12	19	32	100	14.2	29	34	M 14	0.38
60S-12	22	32	150		32	50		0.68
25S-58	16	32	63		22	12		0.17
40S-58	19	38	100	17.0	31	26	M 16	0.42
60S-58	22	38	150		40	47		0.72
40S-34	19	38	100		33	27		0.38
60S-34	25	38	150	21.0	43	44	M 18	0.76
80S-34	25	50	200		55	65	M 20	1.52
60S-10	30		150		43	38		1.29
80S-10	32	50	200	26.0	53	57	M 22	2.00
10S-10	38		250		60	64	M 24	2.95

Z-ステップクランプ

Z-TYPE STEP CLAMP



- 材質 S45C
 - 仕上 黒染
- (2ヶ1組)







(寸法表) 単位 長さ(mm) 質量約(kg)

No.	A	B	C	D	E	F	G	H	I	使用 ボルト	質量 (1組)
35Z-12	16	28	88	17		42	13.5	13	16		0.37
45Z-12	19	32	113	17	14.5	55	20.5	18	19	M14	0.59
60Z-12	22	32	150	20		62	35.5	22	22		0.89

治工具用クランプ

JIG CLAMP



- 材質 S45C
 - 硬度 HRC30~35° (本体)
 - 仕上 黒染
- (2ヶ1組)

(寸法表) 単位 長さ(mm) 質量約(kg)

No.	A	B	C	D	E	F	G	H	I	J	K(受ネジ)	使用ボルト	T-ナット	質量(1組)
JC-1	9	22	90	25.5	33	7	7	60	0.5	10	KS-6	M 6-75	1006-TN	0.5
JC-2	12	25	100	29.5	33	9	16	60	1.0	12	KS-8	M 8-90	1008-TN	0.8
JC-3	16	25	115	33.5	39	11	18	76	1.0	15	KS-10	M 10-100	1210-TN	9.0
JC-4	19	32	140	40.5	45	15	20	90	1.5	20	KS-14	M 14-110	1614-TN	2.0