

Reamers

Endmills

Drills

Countersinks/  
Counterbores

Slitting Saws/  
Cut-off tools

Cutters

Side  
Milling

Staggered

Angle

Plain

for Pipe

SS

千鳥刃サイドカッター  
Staggered Side Milling Cutters



厚み(T)の寸法許容差  
Tolerance of thickness(T)

厚み(T) Thickness(T)	許容差 Tolerance
3.0以下 3.0 or less	+0.060 0
3.0をこえ6.0以下 6.0 or less exceeding 3.0	+0.075 0
6.0をこえ10.0以下 10.0 or less exceeding 6.0	+0.090 0
10.0をこえ18.0以下 18.0 or less exceeding 10.0	+0.110 0
18.0をこえ30.0以下 30.0 or less exceeding 18.0	+0.130 0
30.0をこえ50.0以下 50.0 or less exceeding 30.0	+0.160 0

- 外径、厚みが豊富  
Wide variety of diameters and thicknesses
- 重切削加工に最適  
Ideal for heavy cutting
- MCO材(コバルト高速度鋼)を使用  
Uses MCO material (Cobalt high-speed steel)

穴径φ25.4 Hole Dia.φ25.4

品番 Product No.	寸法 Size				標準価格 Standard price ¥
	刃径 D	厚み T	穴径 d	刃数 NT	
SST075X030	75	3	25.4	18	16,000
SST075X035	75	3.5	25.4	18	16,000
SST075X040	75	4	25.4	18	14,700
SST075X045	75	4.5	25.4	18	13,000
SST075X050	75	5	25.4	18	13,000
SST075X055	75	5.5	25.4	18	12,600
SST075X060	75	6	25.4	18	12,600
SST075X065	75	6.5	25.4	18	14,000
SST075X070	75	7	25.4	18	14,000
SST075X075	75	7.5	25.4	18	14,000
SST075X080	75	8	25.4	18	14,000
SST075X085	75	8.5	25.4	18	15,200
SST075X090	75	9	25.4	18	15,200
SST075X095	75	9.5	25.4	18	15,200
SST075X100	75	10	25.4	18	15,200
SST075X110	75	11	25.4	18	16,500
SST075X120	75	12	25.4	18	16,500
SST075X130	75	13	25.4	16	18,300
SST075X140	75	14	25.4	16	18,300
SST075X150	75	15	25.4	16	20,100
SST075X160	75	16	25.4	16	20,100
SST075X170	75	17	25.4	16	23,400
SST075X180	75	18	25.4	16	23,400
SST075X190	75	19	25.4	16	28,300
SST075X200	75	20	25.4	16	28,300
SST075X210	75	21	25.4	16	29,900
SST075X220	75	22	25.4	16	29,900
SST075X230	75	23	25.4	16	31,500
SST075X240	75	24	25.4	16	31,500

品番 Product No.	寸法 Size				標準価格 Standard price ¥
	刃径 D	厚み T	穴径 d	刃数 NT	
SST075X250	75	25	25.4	16	33,700
SST075X260	75	26	25.4	16	34,400
SST075X270	75	27	25.4	16	34,400
SST075X280	75	28	25.4	16	37,000
SST075X290	75	29	25.4	16	37,000
SST075X300	75	30	25.4	16	37,000
SST075X320	75	32	25.4	16	39,500
SST075X350	75	35	25.4	16	39,500
SST100X030	100	3	25.4	20	22,700
SST100X035	100	3.5	25.4	20	22,700
SST100X040	100	4	25.4	20	20,800
SST100X045	100	4.5	25.4	20	20,800
SST100X050	100	5	25.4	20	20,800
SST100X055	100	5.5	25.4	20	20,000
SST100X060	100	6	25.4	20	20,000
SST100X065	100	6.5	25.4	20	22,300
SST100X070	100	7	25.4	20	22,300
SST100X075	100	7.5	25.4	20	22,300
SST100X080	100	8	25.4	20	22,300
SST100X085	100	8.5	25.4	20	23,800
SST100X090	100	9	25.4	20	23,800
SST100X095	100	9.5	25.4	20	23,800
SST100X100	100	10	25.4	20	23,800
SST100X110	100	11	25.4	20	27,200
SST100X120	100	12	25.4	20	27,200
SST100X130	100	13	25.4	18	30,200
SST100X140	100	14	25.4	18	30,200
SST100X150	100	15	25.4	18	32,900
SST100X160	100	16	25.4	18	32,900