



(Granite surface plate)



GRANITE SURFACE PLATE

STANDARDS

GRANITE SURFACE PLATE

- USE**
- Measurement of flatness, parallelism and squareness
 - For tooling set up, precision inspection etc.

- MATERIAL**
- Granite

- FEATURES**
- Granite is abrasion resistant and unlike cast iron, granite does not rust or deteriorate with time



G6060

Order No.	Model No.	W × D × H (mm)	Flatness (μm)	Weight
151102	G1520	150 × 200 × 50	3	5 kg
151103	G2020	200 × 200 × 50	3	6 kg
151104	G2525	250 × 250 × 70	3	13 kg
151001	G3030	300 × 300 × 100	3	55 kg
151002	G3045	300 × 450 × 100	3	61 kg
151007	G5050	500 × 500 × 100	4	93 kg
151003	G4560	450 × 600 × 100	4	96 kg
151008	G5075	500 × 750 × 130	5	169 kg
151004	G6060	600 × 600 × 130	5	161 kg
151005	G75100	750 × 1000 × 150	7	380 kg
151006	G10100	1000 × 1000 × 150	8	500 kg
151000	G10150	1000 × 1500 × 200	9	980 kg
151105	G10200	1000 × 2000 × 200	12	1500 kg

05


GRANITE SURFACE PLATE STEEL STAND



GT-5075J + G5075

GT-75100J

DIMENSIONS



Units : mm

Model No.	A	B	C	D	E	F
GT-5050J	Approx. 800 ~ 850	100	280	280	485 ~ 515	485 ~ 515
GT-4560J	Approx. 800 ~ 850	100	252	336	435 ~ 465	585 ~ 615
GT-5075J	Approx. 800 ~ 850	130	280	420	485 ~ 515	735 ~ 765
GT-6060J	Approx. 800 ~ 850	130	336	336	585 ~ 615	585 ~ 615
GT-75100J	Approx. 800 ~ 850	150	420	560	735 ~ 765	985 ~ 1015
GT-10100J	Approx. 800 ~ 850	150	560	560	985 ~ 1015	985 ~ 1015
GT-10150J	Approx. 800 ~ 850	200	560	840	985 ~ 1015	1485 ~ 1515

- USE**
- Steel stand for SK granite surface plate

- MATERIAL**
- Angle steel

- FEATURES**
- Heavy duty bolted steel construction
 - Leveling bolts for horizontal adjustment
 - Gray painted frame

Order No.	Model No.	Applicable Surface Plate Size (mm)	W × D × H (mm)	Weight
151241	GT-5050J	500 × 500 × 100	380 × 380 × 775 ~ 800	17.5kg
151242	GT-4560J	450 × 600 × 100	350 × 400 × 775 ~ 800	17.5kg
151243	GT-5075J	500 × 750 × 130	380 × 515 × 775 ~ 800	18.5kg
151244	GT-6060J	600 × 600 × 130	420 × 440 × 775 ~ 800	18.5kg
151245	GT-75100J	750 × 1000 × 150	530 × 660 × 775 ~ 800	48kg
151246	GT-10100J	1000 × 1000 × 150	640 × 700 × 675 ~ 700	50kg
151247	GT-10150J	1000 × 1500 × 200	700 × 940 × 675 ~ 700	60kg

STANDARDS

GRANITE

CAST IRON SURFACE PLATE

PARALLEL BLOCK

V BLOCK

SQUARE

STRAIGHT EDGE

PARALLEL CLAMPS