

## List of Motor and Control Unit Combinations

Model numbers for motor and control unit combinations are shown below.

### Single-Phase 110/115 VAC

| Output Power<br>HP | Power<br>W | Package Model     | Motor Model | Control Unit Model |
|--------------------|------------|-------------------|-------------|--------------------|
| 1/125              | 6          | <b>US206-401U</b> | USM206-401W | USP206-1U          |
|                    |            | <b>US206-001U</b> | USM206-001W | USP206-1U          |
| 1/50               | 15         | <b>US315-401U</b> | USM315-401W | USP315-1U          |
|                    |            | <b>US315-001U</b> | USM315-001W | USP315-1U          |
| 1/30               | 25         | <b>US425-401U</b> | USM425-401W | USP425-1U          |
|                    |            | <b>US425-001U</b> | USM425-001W | USP425-1U          |
| 1/19               | 40         | <b>US540-401U</b> | USM540-401W | USP540-1U          |
|                    |            | <b>US540-001U</b> | USM540-001W | USP540-1U          |
| 1/12               | 60         | <b>US560-501U</b> | USM560-501W | USP560-1U          |
|                    |            | <b>US560-001U</b> | USM560-001W | USP560-1U          |
| 1/8                | 90         | <b>US590-501U</b> | USM590-501W | USP590-1U          |
|                    |            | <b>US590-001U</b> | USM590-001W | USP590-1U          |

### Single-Phase 220/230 VAC


| Output Power<br>HP | Power<br>W | Package Model     | Motor Model | Control Unit Model |
|--------------------|------------|-------------------|-------------|--------------------|
| 1/125              | 6          | <b>US206-402E</b> | USM206-402W | USP206-2E          |
|                    |            | <b>US206-002E</b> | USM206-002W | USP206-2E          |
| 1/50               | 15         | <b>US315-402E</b> | USM315-402W | USP315-2E          |
|                    |            | <b>US315-002E</b> | USM315-002W | USP315-2E          |
| 1/30               | 25         | <b>US425-402E</b> | USM425-402W | USP425-2E          |
|                    |            | <b>US425-002E</b> | USM425-002W | USP425-2E          |
| 1/19               | 40         | <b>US540-402E</b> | USM540-402W | USP540-2E          |
|                    |            | <b>US540-002E</b> | USM540-002W | USP540-2E          |
| 1/12               | 60         | <b>US560-502E</b> | USM560-502W | USP560-2E          |
|                    |            | <b>US560-002E</b> | USM560-002W | USP560-2E          |
| 1/8                | 90         | <b>US590-502E</b> | USM590-502W | USP590-2E          |
|                    |            | <b>US590-002E</b> | USM590-002W | USP590-2E          |

## Extension Cable (Sold separately)

When installing the motor and control unit in different locations, an extension cable can be used (sold separately). This enables remote operation at a distance of up to 15.7 feet. (4.75 m).

### Applicable Products: US206, US315, US425, US540

| Model            | Length: L ft. (m) |
|------------------|-------------------|
| <b>CC01SS052</b> | 3.3 (1)           |
| <b>CC02SS052</b> | 6.6 (2)           |
| <b>CC03SS052</b> | 9.8 (3)           |
| <b>CC04SS052</b> | 13.1 (4)          |



### Applicable Products: US560, US590

| Model          | Length: L ft. (m) |
|----------------|-------------------|
| <b>CC01SS2</b> | 3.3 (1)           |
| <b>CC02SS2</b> | 6.6 (2)           |
| <b>CC03SS2</b> | 9.8 (3)           |
| <b>CC04SS2</b> | 13.1 (4)          |

