




GTW-5075J



DIMENSIONS



Units : mm

DIMENSIONS	Model No.	A	B	C	D	E	F
①	GTW-5050J	Approx. 800 ~ 850	100	140	280	485 ~ 515	485 ~ 515
①	GTW-4560J	Approx. 800 ~ 850	100	126	336	440 ~ 465	590 ~ 615
①	GTW-6060J	Approx. 800 ~ 850	130	168	336	590 ~ 615	590 ~ 615
①	GTW-5075J	Approx. 800 ~ 850	130	140	420	485 ~ 515	735 ~ 765
②	GTW-75100J	Approx. 800 ~ 850	150	210	560	730 ~ 770	980 ~ 1020
②	GTW-10100J	Approx. 800 ~ 850	150	280	560	980 ~ 1040	980 ~ 1040
③	GTW-10150W	Approx. 800 ~ 850	200	280	420	980 ~ 1040	1480 ~ 1540
③	GT-10200W	Approx. 800 ~ 850	200	280	560	980 ~ 1040	1980 ~ 2040

USE

- Designed to fit SK granite surface plate

MATERIAL

- Square tubular machine grade steel

FEATURES

- Leveling bolts for horizontal adjustment
- Side stop arms
- Casters for easy movement

STANDARDS

GRANITE

CAST IRON SURFACE PLATE

PARALLEL BLOCK

V BLOCK

SQUARE

STRAIGHT EDGE

PARALLEL CLAMPS

Order No.	Model No.	Surface Plate Size (mm)	Weight
151253	GTW-5050J	500 × 500 × 100	29kg
151254	GTW-4560J	450 × 600 × 100	30kg
151255	GTW-6060J	600 × 600 × 130	33kg
151256	GTW-5075J	500 × 750 × 130	31kg
151257	GTW-75100J	750 × 1000 × 150	43kg
151258	GTW-10100J	1000 × 1000 × 150	50kg
151259	GTW-10150W	1000 × 1500 × 200	77kg
151260	GT-10200W	1000 × 2000 × 200	102kg