



溶接式180° ベンド/溶接式チーズ/溶接式ローネックチーズ
180 Bend both end Weld/Type TEE-W/Type TEEV-W

溶接式 180° ベンド
Type 18BND-W


180° Bend both end Weld



Nom.size	OD	t	A	B	Mass kg
1.5 ^S	38.1	1.2	152.4	76.2	0.28
2.0 ^S	50.8	1.5	152.4	76.2	0.47
2.5 ^S	63.5	2	190.6	95.3	1.05
3.0 ^S	76.3	2	254	127	1.65
4.0 ^S	101.6	2	254	127	1.98

溶接式チーズ
Type TEE-W

Tee ends Weld




※SUS316Lのみ
Only SUS316L

Nom.size	OD	t	A	Mass kg
1.0 ^S	25.4	1.2	33.5	0.06
1.25 ^S	31.8	1.2	38	0.09
1.5 ^S	38.1	1.2	48.5	0.13
2.0 ^S	50.8	1.5	60.5	0.25
2.5 ^S	63.5	2	83.5	0.61
3.0 ^S	76.3	2	88.5	0.77
3.5 ^S	89.1	2	103.5	1.04
4.0 ^S	101.6	2	127	1.49
4.5 ^S	114.3	3	115	2.74
5.5 ^S	139.8	3	140	4.69
6.5 ^S	165.2	3	165	6.71
Nom.size	OD	t	A	Mass kg
※ 8A	13.8	1.65	38	0.05
※ 10A	17.3	1.65	38	0.061
※ 15A	21.7	2.1	38	0.095

溶接式ローネックチーズ
Type TEEV-W

Tee ends Weld (Low Neck)



※SUS316Lのみ
Only SUS316L

Nom.size	OD	t	A	B	Mass kg
1.0 ^S	25.4	1.2	33.5	14	0.048
1.5 ^S	38.1	1.2	48.5	21	0.101
2.0 ^S	50.8	1.5	60.5	28	0.199
2.5 ^S	63.5	2	83.5	34	0.506
3.0 ^S	76.3	2	88.5	40.5	0.638
Nom.size	OD	t	A	B	Mass kg
※ 8A	13.8	1.65	38	13	—
※ 10A	17.3	1.65	38	15	—
※ 15A	21.7	2.1	38	17	—