


1方ヘルール異径ローネックチーズ／ヘルールローネックチーズ
Reducing Tee ends Weld/Ferrule/Weld(Low Neck)/Tee ends Ferrule(Low Neck)

1方ヘルール異径ローネックチーズ

Reducing Tee ends Weld/Ferrule/Weld(Low Neck)

Type TEEVX-WCW





※SUS316Lのみ
Only SUS316L

Nom.size	ID1	ID2	A	B
※ 1.0 ^S ×8A	23	10.5	33.5	31
※ 1.0 ^S ×10A	23	14	33.5	31
※ 1.0 ^S ×15A	23	17.5	33.5	30.5
※ 1.5 ^S ×8A	35.7	10.5	48.5	38
※ 1.5 ^S ×10A	35.7	14	48.5	37.5
※ 1.5 ^S ×15A	35.7	17.5	48.5	37.5
1.5 ^S ×1.0 ^S	35.7	23	48.5	42
2.0 ^S ×1.0 ^S	47.8	23	60.5	50
2.0 ^S ×1.5 ^S	47.8	35.7	60.5	49
2.5 ^S ×1.0 ^S	59.5	23	83.5	57.5
2.5 ^S ×1.5 ^S	59.5	35.7	83.5	58
2.5 ^S ×2.0 ^S	59.5	47.8	83.5	58
3.0 ^S ×1.0 ^S	72.3	23	88.5	64.5
3.0 ^S ×1.5 ^S	72.3	35.7	88.5	66
3.0 ^S ×2.0 ^S	72.3	47.8	88.5	65
3.0 ^S ×2.5 ^S	72.3	59.5	88.5	62.5
3.5 ^S ×1.0 ^S	85.1	23	103.5	70.5
3.5 ^S ×1.5 ^S	85.1	35.7	103.5	71.5
4.0 ^S ×1.0 ^S	97.6	23	127	77
4.0 ^S ×1.5 ^S	97.6	35.7	127	77.5

ヘルールローネックチーズ

Tee ends Ferrule(Low Neck)

Type TEEV-3C



Nom.size	ID	A	B	Mass kg
1.0 ^S	23	55	35.5	0.268
1.25 ^S	29.4	55	35	—
1.5 ^S	35.7	70	42.5	0.261
2.0 ^S	47.8	82	49.5	0.457
2.5 ^S	59.5	105	55.5	—
3.0 ^S	72.3	110	62	—
3.5 ^S	85.1	125	69	—
4.0 ^S	97.6	155	81.5	—
Nom.size	ID	A	B	Mass kg
8A	10.5	55	30	—
10A	14	55	32	—
15A	17.5	55	34	—