




LEVER COUPLINGS ステンレス

OZ-A メスネジ型アダプター

ADAPTER FEMALE THREAD




呼び径	mm	15	20	25	32	40	50	65	80	100	125	150	200
	inch	1/2	3/4	1	1 1/4	1 1/2	2	2 1/2	3	4		6	
M		1/2B	3/4B	1B	1 1/4B	1 1/2B	2B	2 1/2B	3B	4B		6B	
ΦD		32	32	37	45	53	63	76	92	120		176	
ΦE		14	21	24	28	36	45	56	72	97		148	
K		33	33	38	48	55	67	85	96	127		168	
h		26	26	34	40	41	48	49	51	53		60	
H		40	40	49	54	56	62	85	70	78		86	

単位:mm

OZ-F オスネジ型アダプター

ADAPTER MALE THREAD




呼び径	mm	15	20	25	32	40	50	65	80	100	125	150
	inch	1/2	3/4	1	1 1/4	1 1/2	2	2 1/2	3	4		6
M		1/2B	3/4B	1B	1 1/4B	1 1/2B	2B	2 1/2B	3B	4B		6B
ΦD		32	32	37	45	53	63	76	92	120		176
ΦE		14	21	24	28	36	45	56	72	97		148
K		33	33	38	48	55	65	82	96	127		192
h1		26	26	34	40	41	48	49	51	53		58
h2		19	19	23	23	23	25	31	36	32		
H		60	60	71	78	79	88	99	102	114		127

単位:mm

OZ-E ホースシャングアダプター

ADAPTER HOSE SHANK



呼び径	mm	20	25	32	40	50	65	80	100	125	150	200
	inch	3/4	1	1 1/4	1 1/2	2	2 1/2	3	4		6	
ΦD		32	37	45	53	63	76	92	120		176	
ΦF		14	19	25	41	43	56	68	92		142	
ΦG		19	25	32	38	50	63	75	101		152	
ΦI		21	27	34	40	53	67	79	105		155	
h1		27	34	40	43	48	50	51	53		60	
h2		51	60	64	66	77	86	102	110		142	
H		89	104	115	117	137	150	167	178		221	

単位:mm