


プッシュワン®Eシリーズ

90°メスエルボ


●ミリサイズ



品番	適用チューブ外径 (mm)	Tねじサイズ (Rc)	L1 (mm)	L2 (mm)	L3 (mm)	L4 (mm)	A (mm)	Fチューブ挿入長さ (mm)	H×φ二面幅 (mm)	D (mm)	最小内径 (mm)	有効断面積 (mm ²)	質量 (g)
EFL4-PT1/8	4	Rc1/8	17.2	21.7	24.9	22.1	8.0	13	14.0×15.4	9.8	3.0	—	13.0
EFL6-PT1/8	6	Rc1/8	18.5	24.2	26.2	30.5	8.0	15	14.0×15.4	12.6	5.0	—	15.0
EFL6-PT1/4	6	Rc1/4	18.5	28.2	27.8	34.5	12.0	15	17.0×18.5	12.6	5.0	—	23.0
EFL6-PT3/8	6	Rc3/8	18.5	28.7	30.8	35.0	12.5	15	22.0×24.5	12.6	5.0	—	37.0
EFL8-PT1/8	8	Rc1/8	20.7	25.2	28.4	32.5	8.0	16	14.0×15.4	14.6	7.0	—	17.0
EFL8-PT1/4	8	Rc1/4	20.7	29.2	30.0	36.5	12.0	16	17.0×18.5	14.6	7.0	—	25.0
EFL8-PT3/8	8	Rc3/8	20.7	29.7	33.0	37.0	12.5	16	22.0×24.5	14.6	7.0	—	38.0
EFL10-PT1/4	10	Rc1/4	24.7	32.2	34.0	41.0	12.0	19	17.0×18.5	17.5	9.0	—	29.0
EFL10-PT3/8	10	Rc3/8	24.7	33.7	37.0	42.5	12.5	19	22.0×24.5	17.5	9.0	—	45.0
EFL12-PT3/8	12	Rc3/8	26.3	36.2	38.6	46.2	12.5	20	22.0×24.5	20.0	10.0	—	49.0
EFL12-PT1/2	12	Rc1/2	26.3	39.2	39.6	49.2	15.5	20	24.0×26.5	20.0	10.0	—	54.0


90°ロングエルボ

●ミリサイズ



品番	適用チューブ外径 (mm)	Tねじサイズ (M,R)	L1 (mm)	L2 (mm)	L3 (mm)	L4 (mm)	A (mm)	Fチューブ挿入長さ (mm)	H×φ二面幅 (mm)	D (mm)	d1 (mm)	最小内径 (mm)	有効断面積 (mm ²)	質量 (g)
ELL4-M5	4	M5×0.8	17.2	29.9	22.7	34.8	4.0	13	10.0×11.0	9.8	2.0	2.0	3.0	13.0
ELL4-PT1/8	4	R1/8	17.2	32.4	22.7	37.3	8.0	13	10.0×11.0	9.8	5.0	3.0	4.0	14.0
ELL4-PT1/4	4	R1/4	17.2	36.4	24.9	41.3	11.0	13	14.0×15.4	9.8	7.0	3.0	4.0	27.0
ELL6-M5	6	M5×0.8	18.5	34.7	25.0	41.0	4.0	15	12.0×13.0	12.6	2.0	2.0	3.5	20.0
ELL6-PT1/8	6	R1/8	18.5	37.2	25.0	43.5	8.0	15	12.0×13.0	12.6	5.0	5.0	12.0	22.0
ELL6-PT1/4	6	R1/4	18.5	41.2	26.2	47.5	11.0	15	14.0×15.4	12.6	7.0	5.0	12.0	31.0
ELL6-PT3/8	6	R3/8	18.5	42.2	27.8	48.5	12.0	15	17.0×18.5	12.6	9.0	5.0	12.0	45.0
ELL8-PT1/8	8	R1/8	20.7	40.2	28.4	47.5	8.0	16	14.0×15.4	14.6	5.0	5.0	18.5	30.0
ELL8-PT1/4	8	R1/4	20.7	44.2	28.4	51.5	11.0	16	14.0×15.4	14.6	7.0	7.0	23.0	35.0
ELL8-PT3/8	8	R3/8	20.7	45.2	30.0	52.5	12.0	16	17.0×18.5	14.6	9.0	7.0	23.0	50.0
ELL10-PT1/8	10	R1/8	24.7	46.2	33.9	55.0	8.0	19	17.0×18.5	17.5	5.0	5.0	22.0	48.0
ELL10-PT1/4	10	R1/4	24.7	50.2	33.9	59.0	11.0	19	17.0×18.5	17.5	7.0	7.0	34.5	53.0
ELL10-PT3/8	10	R3/8	24.7	51.2	33.9	60.0	12.0	19	17.0×18.5	17.5	9.0	9.0	37.0	59.0
ELL10-PT1/2	10	R1/2	24.7	55.2	36.9	64.0	15.0	19	22.0×24.5	17.5	12.0	9.0	37.0	94.0
ELL12-PT1/4	12	R1/4	26.3	55.2	36.8	65.2	11.0	20	19.0×21.0	20.0	7.0	7.0	36.0	72.0
ELL12-PT3/8	12	R3/8	26.3	56.2	36.8	66.2	12.0	20	19.0×21.0	20.0	9.0	9.0	43.0	78.0
ELL12-PT1/2	12	R1/2	26.3	60.2	38.6	70.2	15.0	20	22.0×24.5	20.0	12.0	10.0	43.0	105.0

●インチサイズ



品番	適用チューブ外径 (inch)	Tねじサイズ (M,R)	L1 (mm)	L2 (mm)	L3 (mm)	L4 (mm)	A (mm)	Fチューブ挿入長さ (mm)	H×φ二面幅 (mm)	D (mm)	d1 (mm)	最小内径 (mm)	有効断面積 (mm ²)	質量 (g)
ELL1/4-M5	1/4	M5×0.8	18.1	34.7	24.6	41.0	4.0	15	12.0×13.0	13.0	2.0	2.0	3.0	20.0
ELL1/4-PT1/8	1/4	R1/8	18.1	37.2	24.6	43.5	8.0	15	12.0×13.0	13.0	5.0	5.0	13.0	22.0
ELL1/4-PT1/4	1/4	R1/4	18.1	41.2	25.8	47.5	11.0	15	14.0×15.4	13.0	7.0	5.0	13.0	31.0
ELL5/16-PT1/8	5/16	R1/8	20.6	40.2	28.3	47.5	8.0	16	14.0×15.4	15.0	5.0	5.0	18.5	30.0
ELL5/16-PT1/4	5/16	R1/4	20.6	44.2	28.3	51.5	11.0	16	14.0×15.4	15.0	7.0	7.0	23.0	35.0
ELL5/16-PT3/8	5/16	R3/8	24.4	45.2	29.9	52.5	12.0	19	17.0×18.5	18.0	9.0	7.0	—	—
ELL3/8-PT1/4	3/8	R1/4	24.4	50.2	33.7	59.0	11.0	19	17.0×18.5	18.0	7.0	7.0	30.0	53.0
ELL3/8-PT3/8	3/8	R3/8	24.4	51.2	33.7	60.0	12.0	19	17.0×18.5	18.0	9.0	9.0	32.0	59.0
ELL1/2-PT1/4	1/2	R1/4	26.5	55.2	37.0	65.7	11.0	21	19.0×21.0	21.5	7.0	7.0	37.0	72.0
ELL1/2-PT3/8	1/2	R3/8	26.5	56.2	37.0	66.7	12.0	21	19.0×21.0	21.5	9.0	9.0	53.0	78.0
ELL1/2-PT1/2	1/2	R1/2	26.5	60.2	38.7	70.7	15.0	21	22.0×24.5	21.5	12.0	10.0	55.5	105.0

☞ インチサイズにはめっき処理をしません。

チューブ

クリップ
チューブ

加工チューブ

プッシュワン
継手

クイックシール
継手

クリーン継手
ケミファイナット

竹のこ継手

制御切替着脱
シリーズ

治具・工具
付属品

技術資料

参考資料