




# LEVER COUPLINGS ポリプロピレン

## OZ-A メスネジ型アダプター

### ADAPTER FEMALE THREAD




呼び径	mm	20	25	32	40	50	80
	inch	3/4	1	1 1/4	1 1/2	2	3
M		3/4B	1B	1 1/4B	1 1/2B	2B	3B
ΦD		32	37	45	53	63	92
ΦE		19	22	28	33	42	71
K		36	43	51	60	76	106
h1		29	35	40	41	50	52
h2		21	27	25	28	30	38
H		50	62	65	69	80	90

単位:mm

## OZ-F オスネジ型アダプター

### ADAPTER MALE THREAD




呼び径	mm	20	25	32	40	50	80
	inch	3/4	1	1 1/4	1 1/2	2	3
M		3/4B	1B	1 1/4B	1 1/2B	2B	3B
ΦD		32	37	45	53	63	92
ΦE		17	22	29	33	43	72
K		36	43	52	60	67	98
h1		29	35	40	43	48	51
h2		24	33	25	30	34	39
H		62	82	78	85	96	109

単位:mm

## OZ-E ホースシャンクアダプター

### ADAPTER HOSE SHANK




呼び径	mm	20	25	32	40	50	80
	inch	3/4	1	1 1/4	1 1/2	2	3
ΦD		32	37	45	53	63	92
ΦE		19	22	28	34	45	71
ΦF		13	21	23	30	40	60
ΦG		19	25	31	37	50	75
ΦI		21	27	33	40	52	79
h1		41	43	64	71	72	102
h2		28	34	38	40	48	50
H		80	93	113	123	130	172

単位:mm

## OZ-DP ダストプラグ

### ADAPTER DUST PLUG



呼び径	mm	20	25	32	40	50	80
	inch	3/4	1	1 1/4	1 1/2	2	3
ΦD		32	37	45	53	63	92
ΦE		16	22	29	38	47	71
H		33	38	41	18	54	59
L		10	13	12	16	18	16
H		43	51	53	64	72	75

単位:mm