



ティー



Mねじ



●ミリサイズ


品番	適用チューブ外径 (mm)	Tねじサイズ (R・M)	L1 (mm)	L2 (mm)	L4 (mm)	L5 (mm)	A (mm)	Fチューブ挿入長さ (mm)	H×φ二面幅 (mm)	D (mm)	d1 (mm)	最小内径 (mm)	有効断面積 (mm ²)	質量 (g)
ET3-M5-C1S	3	M5×0.8	12.5	13.0	16.0	25.0	3.5	11	7.0×7.7	6.3	2.5	1.5	1.5	2.0
ET4-M5-C1S	4	M5×0.8	17.7	20.2	25.1	35.3	4.0	14	10.0×11.0	10.0	2.0	2.0	3.0	8.0
ET4-R1/8-C1S	4	R1/8	17.7	23.7	28.6	35.3	9.0	14	10.0×11.0	10.0	5.0	3.0	4.0	10.0
ET6-M5-C1S	6	M5×0.8	18.9	22.7	29.0	37.9	4.0	15	12.0×13.0	13.0	2.0	2.0	3.5	12.0
ET6-R1/8-C1S	6	R1/8	18.9	26.2	32.5	37.9	9.0	15	12.0×13.0	13.0	4.5	4.5	12.0	14.0
ET6-R1/4-C1S	6	R1/4	18.9	30.2	36.5	37.9	12.0	15	14.0×15.4	13.0	7.0	4.5	12.0	21.0
ET8-R1/8-C1S	8	R1/8	21.1	29.2	36.5	42.2	9.0	16	14.0×15.4	15.0	6.0	6.0	18.5	18.0
ET8-R1/4-C1S	8	R1/4	21.1	31.2	38.5	42.2	12.0	16	14.0×15.4	15.0	6.5	6.5	23.0	24.0
ET10-R1/4-C1S	10	R1/4	25.0	37.2	46.0	50.0	12.0	19	17.0×18.5	18.0	8.0	8.0	34.5	34.0
ET10-R3/8-C1S	10	R3/8	25.0	37.2	46.0	50.0	14.0	19	17.0×18.5	18.0	9.0	8.0	37.0	39.0
ET12-R3/8-C1S	12	R3/8	26.7	38.7	48.8	53.4	14.0	20	19.0×21.0	20.5	10.0	10.0	43.0	48.0
ET12-R1/2-C1S	12	R1/2	26.7	41.7	51.8	53.4	16.0	20	22.0×24.0	20.5	12.0	9.5	43.0	65.0

※受注生産品


●インチサイズ

品番	適用チューブ外径 (inch)	Tねじサイズ (M)	L1 (mm)	L2 (mm)	L4 (mm)	L5 (mm)	A (mm)	Fチューブ挿入長さ (mm)	H×φ二面幅 (mm)	D (mm)	d1 (mm)	最小内径 (mm)	有効断面積 (mm ²)	質量 (g)
ET1/8-M5-C1S	1/8	M5×0.8	17.6	26.2	32.5	35.2	9.0	15	12.0×13.0	13.0	4.5	4.5	13.0	5.0

サービスティー



Mねじ



●ミリサイズ

品番	適用チューブ外径 (mm)	Tねじサイズ (R・M)	L1 (mm)	L2 (mm)	L6 (mm)	L7 (mm)	L8 (mm)	A (mm)	Fチューブ挿入長さ (mm)	H×φ二面幅 (mm)	D (mm)	d1 (mm)	最小内径 (mm)	有効断面積 (mm ²)	質量 (g)
EST4-M5-C1S	4	M5×0.8	17.7	20.2	17.7	37.9	23.2	4.0	14	10.0×11.0	10.0	2.0	2.0	3.0	8.0
EST4-R1/8-C1S	4	R1/8	17.7	23.7	17.7	40.4	23.2	9.0	14	10.0×11.0	10.0	5.0	3.0	4.0	10.0
EST6-M5-C1S	6	M5×0.8	18.9	27.7	18.9	41.6	25.4	4.0	15	12.0×13.0	13.0	2.0	2.0	3.5	12.0
EST6-R1/8-C1S	6	R1/8	18.9	26.2	18.9	44.1	25.4	9.0	15	12.0×13.0	13.0	4.5	4.5	12.0	14.0
EST6-R1/4-C1S	6	R1/4	18.9	30.2	18.9	48.1	26.6	12.0	15	14.0×15.4	13.0	7.0	4.5	12.0	21.0
EST8-R1/8-C1S	8	R1/8	21.1	29.2	21.1	48.3	28.8	9.0	16	14.0×15.4	15.0	6.0	6.0	18.5	18.0
EST8-R1/4-C1S	8	R1/4	21.1	31.2	21.1	52.3	28.8	12.0	16	14.0×15.4	15.0	6.5	6.5	23.0	24.0
EST10-R1/4-C1S	10	R1/4	25.0	37.2	25.0	62.2	34.3	12.0	19	17.0×18.5	18.0	8.0	8.0	34.5	34.0
EST10-R3/8-C1S	10	R3/8	25.0	37.2	25.0	62.2	34.3	14.0	19	17.0×18.5	18.0	9.0	8.0	37.0	40.0
EST12-R3/8-C1S	12	R3/8	26.7	38.7	26.7	65.4	37.2	14.0	20	19.0×21.0	20.5	10.0	10	43.0	48.0
EST12-R1/2-C1S	12	R1/2	26.7	41.7	26.7	68.4	38.7	16.0	20	22.0×24.0	20.5	12.0	9.5	43.0	65.0

※受注生産品

チューブ

クリップ

加工チューブ

プッシュダウン

クイックシール

クリップ継手

竹のこ継手

制御切替着脱

治具・工具

技術資料

参考資料