


BR

ブリッジリーマ
Bridge Reamers



※先端食付き角55° Point 55° Chamfer

- リーマ代が大きい場合に使用
For large removal Amount
- MCO材(コバルト高速度鋼)を使用
Uses MCO material (Cobalt high-speed steel)

※MT1・4・5は生産終了につき在庫限りとなります。

品番 Product No.	寸法 Size					標準価格 Standard price ¥
	刃径 D	シャンク No.	刃長 ℓ	全長 L	刃数 NT	
BR080	8.0	MT1	70	145	5	8,700
BR085	8.5	MT1	70	145	5	8,700
BR090	9.0	MT1	75	150	5	8,700
BR095	9.5	MT1	75	150	5	9,000
BR100	10.0	MT1	85	160	5	9,000
BR105	10.5	MT1	85	160	5	9,700
BR110	11.0	MT1	95	170	5	9,700
BR115	11.5	MT1	95	170	5	9,700
BR120	12.0	MT1	105	180	5	9,700
BR125	12.5	MT1	105	180	5	10,900
BR130	13.0	MT1	105	180	5	10,900
BR135	13.5	MT1	105	180	5	11,900
BR140	14.0	MT2	110	200	5	12,500
BR145	14.5	MT2	110	200	5	13,000
BR150	15.0	MT2	110	200	5	13,000
BR155	15.5	MT2	110	200	5	13,700
BR160	16.0	MT2	110	200	5	13,700
BR165	16.5	MT2	110	200	5	15,700
BR170	17.0	MT2	120	210	5	15,700
BR175	17.5	MT2	120	210	5	15,700
BR180	18.0	MT2	120	210	5	15,700
BR185	18.5	MT2	120	210	5	20,800
BR190	19.0	MT2	120	210	5	20,800
BR195	19.5	MT3	140	260	5	20,800
BR200	20.0	MT3	140	260	5	20,800
BR205	20.5	MT3	140	260	5	22,200
BR210	21.0	MT3	155	270	5	22,200
BR215	21.5	MT3	155	270	5	22,200
BR220	22.0	MT3	155	270	5	22,200
BR225	22.5	MT3	155	270	5	25,300
BR230	23.0	MT3	155	270	5	25,300
BR235	23.5	MT3	155	270	5	25,300
BR240	24.0	MT3	165	280	5	25,300
BR245	24.5	MT3	165	280	5	27,700

品番 Product No.	寸法 Size					標準価格 Standard price ¥
	刃径 D	シャンク No.	刃長 ℓ	全長 L	刃数 NT	
BR250	25.0	MT3	165	280	5	27,700
BR255	25.5	MT3	165	280	6	30,000
BR260	26.0	MT3	180	310	6	30,000
BR265	26.5	MT3	180	310	6	36,000
BR270	27.0	MT3	180	310	6	36,000
BR275	27.5	MT3	180	310	6	36,000
BR280	28.0	MT3	180	310	6	36,000
BR285	28.5	MT3	180	310	6	40,200
BR290	29.0	MT3	190	320	6	40,200
BR295	29.5	MT3	190	320	6	40,200
BR300	30.0	MT3	190	320	6	40,200
BR305	30.5	MT3	190	320	6	40,200
BR310	31.0	MT3	190	320	6	48,400
BR315	31.5	MT3	190	320	6	49,500
BR320	32.0	MT3	190	320	6	49,500
BR325	32.5	MT4	195	350	7	57,200
BR330	33.0	MT4	195	350	7	57,200
BR335	33.5	MT4	195	350	7	62,200
BR340	34.0	MT4	195	350	7	62,200
BR345	34.5	MT4	195	350	7	66,600
BR350	35.0	MT4	195	350	7	66,600
BR355	35.5	MT4	195	350	7	71,100
BR360	36.0	MT4	215	370	7	71,100
BR365	36.5	MT4	215	370	7	75,500
BR370	37.0	MT4	215	370	7	75,500
BR375	37.5	MT4	215	370	7	78,600
BR380	38.0	MT4	215	370	7	78,600
BR385	38.5	MT4	215	370	7	85,100
BR390	39.0	MT4	225	380	7	85,100
BR395	39.5	MT4	225	380	7	91,700
BR400	40.0	MT4	225	380	7	91,700
BR405	40.5	MT4	225	380	7	91,700
BR410	41.0	MT4	225	380	7	91,700
BR415	41.5	MT4	225	380	7	93,500