


T-Max® P insert for turning

Rhombic 55°



	ISO CODE	P										M					K					S					ANSI CODE		
		1515	1525	4205	4235	4315	4325	5015	GC30	1115	1125	2015	2025	2035	235	GC15	3005	3205	3210	3215	GC30	H13A	1105	1115	1125	GC15		H13A	S05F
Finishing		15 1/2	DNMG 15 04 04L-K																										DNMG 431L-K
		DNMG 15 04 04R-K		☆																									DNMG 431R-K
		DNMG 15 04 08L-K					☆	☆																					DNMG 432L-K
		DNMG 15 04 08R-K		☆	☆		☆	☆																					DNMG 432R-K
		DNMG 15 06 04L-K					☆	☆																					DNMG 441L-K
		DNMG 15 06 04R-K		☆	☆		☆	☆																					DNMG 441R-K
		DNMG 15 06 08L-K					☆	☆																					DNMG 442L-K
		DNMG 15 06 08R-K		☆	☆		☆	☆																					DNMG 442R-K
		15 1/2	DNGG 15 04 04-SGF							☆	☆												☆	☆	☆	☆	☆	☆	DNGG 431-SGF
		DNGG 15 04 08-SGF								☆	☆												☆	☆	☆	☆	☆	☆	DNGG 432-SGF
		DNGG 15 04 12-SGF								☆	☆												☆	☆	☆	☆	☆	☆	DNGG 433-SGF
		DNGG 15 06 04-SGF								☆	☆												☆	☆	☆	☆	☆	☆	DNGG 441-SGF
		DNGG 15 06 08-SGF								☆	☆												☆	☆	☆	☆	☆	☆	DNGG 442-SGF
		DNGG 15 06 12-SGF								☆	☆												☆	☆	☆	☆	☆	☆	DNGG 443-SGF
			11 3/8	DNMG 11 04 04-SF							☆	☆												☆	☆	☆	☆	☆	DNMG 331-SF
			DNMG 11 04 08-SF								☆	☆												☆	☆	☆	☆	☆	DNMG 332-SF
	15 1/2		DNMG 15 04 04-SF								☆	☆												☆	☆	☆	☆	☆	DNMG 431-SF
			DNMG 15 04 08-SF								☆	☆												☆	☆	☆	☆	☆	DNMG 432-SF
			DNMG 15 04 12-SF								☆	☆												☆	☆	☆	☆	☆	DNMG 433-SF
			DNMG 15 06 04-SF								☆	☆												☆	☆	☆	☆	☆	DNMG 441-SF
			DNMG 15 06 08-SF								☆	☆												☆	☆	☆	☆	☆	DNMG 442-SF
			DNMG 15 06 12-SF								☆	☆												☆	☆	☆	☆	☆	DNMG 443-SF
		15 1/2	DNMG 15 04 04-XF						☆							☆					☆				☆			DNMG 431-XF	
		DNMG 15 04 08-XF							☆							☆					☆				☆			DNMG 432-XF	
DNMG 15 06 04-XF								☆							☆					☆				☆			DNMG 441-XF		
DNMG 15 06 08-XF								☆							☆					☆				☆			DNMG 442-XF		
Medium		11 3/8	DNMG 11 04 04-MMC										☆															DNMG 331-MMC	
			DNMG 11 04 08-MMC											☆														DNMG 332-MMC	
			DNMG 15 04 04-MMC											☆														DNMG 431-MMC	
			DNMG 15 04 08-MMC											☆														DNMG 432-MMC	
	DNMG 15 04 12-MMC												☆														DNMG 433-MMC		
	DNMG 15 06 04-MMC												☆														DNMG 441-MMC		
	15 1/2	DNMG 15 06 08-MMC											☆														DNMG 442-MMC		
		DNMG 15 06 12-MMC											☆														DNMG 443-MMC		
		11 3/8	DNMG 11 04 04-PMC					☆	☆																			DNMG 331-PMC	
			DNMG 11 04 08-PMC					☆	☆																			DNMG 332-PMC	
15 1/2	DNMG 15 04 04-PMC					☆	☆																			DNMG 431-PMC			
	DNMG 15 04 08-PMC					☆	☆																			DNMG 432-PMC			
	DNMG 15 04 12-PMC					☆	☆																			DNMG 433-PMC			
	DNMG 15 06 04-PMC					☆	☆																			DNMG 441-PMC			
	DNMG 15 06 08-PMC					☆	☆																			DNMG 442-PMC			
	DNMG 15 06 12-PMC					☆	☆																			DNMG 443-PMC			

For dimensions, see code key on page I14.

