


# CoroCut® 1-2 insert for profiling

Profiling hardened materials



## CoroCut® 1-edge

	SSC	CW	RE	Ordering code	S H			Dimensions, mm, inch	
					7015	7015	7025	AN	APMX
	F	3.00	1.50	N123F1-0300-RE	☆	☆	☆	7°	0.6
		.118	.059						.024
		3.18	1.59	N123F1-0318-RE	☆	☆		7°	0.6
		.125	.062						.024
	H	4.00	2.00	N123H1-0400-RE	☆	☆	☆	7°	0.6
		.157	.079						.026
		5.00	2.50	N123H1-0500-RE	☆	☆		7°	0.7
		.197	.098						.028
	J	6.00	3.00	N123J1-0600-RE	☆	☆		7°	0.7
		.236	.118						.030
		6.35	3.18	N123J1-0635-RE	☆	☆		7°	0.7
		.250	.125						.030
L	8.00	4.00	N123L1-0800-RE	☆	☆		7°	0.8	
	.315	.157						.033	

SSC = To correspond with SSC on holder.

N = Neutral

Tolerances:

	CWTOLL	CWTOLU	CWTOLL"	CWTOLU"	RETOLL	RETOLU	RETOLL"	RETOLU"
N123x1-RE	-0.02	0.02	-0.0008	.0008	-0.02	0.02	-0.0008	.0008

