


Standard Through-hole Mounting Slide DIP Switches

- Gold-plated twin contacts ensure high reliability.
- Washable, with seal tape available.
- Models with from 1 to 10 poles meet wide needs.

RoHS Compliant



List of Models

Tube packaging

		Type	Flat actuator		Raised actuator
			Standard	With seal tape	
No. of poles	Quantity per tube				
1	130	A6T-1101	A6T-1102	A6T-1104	
2	76	A6T-2101	A6T-2102	A6T-2104	
3	55	A6T-3101	A6T-3102	A6T-3104	
4	42	A6T-4101	A6T-4102	A6T-4104	
5	35	A6T-5101	A6T-5102	A6T-5104	
6	28	A6T-6101	A6T-6102	A6T-6104	
7	25	A6T-7101	A6T-7102	A6T-7104	
8	22	A6T-8101	A6T-8102	A6T-8104	
9	20	A6T-9101	A6T-9102	A6T-9104	
10	18	A6T-0101	A6T-0102	A6T-0104	

Note: Order in multiples of the package quantity.

Ratings/Characteristics

Rating (resistive load)		25 mA at 24 VDC 10 μ A (minimum current) at 3.5 VDC
Ambient operating temperature		-20 to +70°C at 60% max. (with no icing or condensation)
Ambient operating humidity		35% to 95% (at +5 to +35°C)
Insulation resistance		100 M Ω min. (at 250 VDC with insulation tester)
Contact resistance (initial value)		200 m Ω max.
Dielectric strength	Between terminals	500 VAC for 1 min
Vibration resistance	Malfunction	10 to 55 Hz, 1.5-mm double amplitude
Shock resistance	Malfunction	300 m/s ² min.
Durability	Electrical	1,000 operations min.
Washing		Standard models: Not possible, Models with seal tape: Possible, Models with raised actuators: Not possible
Degree of protection		IEC IP40
Operating force		0.29 to 9.8 N {30 to 1,000 gf}
Weight		0.26 g (2 poles), 0.44 g (4 poles), 0.62 g (6 poles), 0.79 g (8 poles), 0.96 g (10 poles)