



CoroCut® XS QS shank tool for parting and grooving

For sliding-head machines



Metric version


					Dimensions								
SSC	CZC _{MS}	CDX	OHX	CNSC	Ordering code	B	H	LF	WF	HF	Nm	Kg	MIID
3	10 x 10	8.5	27	0	QS-SMALR/L 1010E3	10	10	70	10	10	1.2	0.0	MACL 3 200-N
	12 x 12	8.5	27	0	QS-SMALR/L 1212E3	12	12	70	12	12	1.2	0.1	MACL 3 200-N
	16 x 16	8.5	27	0	QS-SMALR/L 1616E3	16	16	70	16	16	1.2	0.1	MACL 3 200-N

Inch version

					Dimensions, inch								
SSC	CZC _{MS}	CDX	OHX	CNSC	Ordering code	B	H	LF	WF	HF	Ft/lbs	Lbs	MIID
3	1/2 x 1/2	.335	1.063	0	QS-SMALR 083X	.500	.500	2.756	.500	.000	0.9	.13	MACR 3 200-N
	5/8 x 5/8	.335	1.063	0	QS-SMALR 103X	.625	.625	2.756	.625	.000	0.9	.24	MACR 3 200-N

SSC = To correspond with SSC on insert.

R = Right hand, L = Left hand



B123



I1



H10



I38