





# SEC-MINI Tool Holders Zero Off-set Holders



Side lever locking holders



Holder


Above figures show right hand tools.

Parts

|       |         |      |       |
|-------|---------|------|-------|
|       |         |      |       |
| LCL06 | BTT0407 | LP07 | TH020 |
| LCL09 | BTT0411 | LP06 |       |

| Cat. No.                 | Stock |   | Dimensions (mm) |    |                |    |                |   | Applicable Insert | Lever Pin | Set Screw | Pin  | Wrench |
|--------------------------|-------|---|-----------------|----|----------------|----|----------------|---|-------------------|-----------|-----------|------|--------|
|                          | R     | L | h               | b  | L <sub>1</sub> | f  | h <sub>1</sub> | e |                   |           |           |      |        |
| <b>PCLC R/L1010-K06X</b> | ●     |   | 10              | 10 | 125            | 10 | 10             | 0 | CC□T0602          | LCL06     | BTT0407   | LP07 | TH020  |
| <b>PCLC R/L1212-K09X</b> | ●     |   | 12              | 12 | 125            | 15 | 12             | 0 | CC□T09T3          | LCL09     | BTT0411   | LP06 | TH020  |
| <b>PCLC R/L1616-K09X</b> | ●     |   | 16              | 16 | 125            | 16 | 16             | 0 | CC□T09T3          |           |           |      |        |

Insert selection From D25



Holder

Above figures show right hand tools.



Parts

|            |       |
|------------|-------|
|            |       |
| BFTX02506N | TRX08 |
| BFTX0409N  | TRX15 |

| Cat. No.                 | Stock |   | Dimensions (mm) |    |                |    |                |   | Applicable Insert | Screw | Recommended Tightening Torque (N·m) | Wrench |
|--------------------------|-------|---|-----------------|----|----------------|----|----------------|---|-------------------|-------|-------------------------------------|--------|
|                          | R     | L | h               | b  | L <sub>1</sub> | f  | h <sub>1</sub> | e |                   |       |                                     |        |
| <b>SCLC R/L1010-H06X</b> | ●     | ● | 10              | 10 | 100            | 10 | 10             | 0 | CC□T0602          | 1.5   | TRX08                               |        |
| <b>SCLC R/L1215-K09X</b> | ●     | ● | 12              | 15 | 125            | 15 | 12             | 0 | CC□T09T3          | 3.4   | TRX15                               |        |
| <b>SCLC R/L1215-F09X</b> | ●     | ● | 12              | 15 | 85             | 15 | 12             | 0 | CC□T09T3          |       |                                     |        |

85mm Shank

Insert selection From D25



Holder

Above figures show right hand tools.

Parts

|            |       |
|------------|-------|
|            |       |
| BFTX02506N | TRX08 |
| BFTX0409N  | TRX15 |

| Cat. No.                 | Stock |   | Dimensions (mm) |    |                |    |                |   | Applicable Insert | Screw | Recommended Tightening Torque (N·m) | Wrench |
|--------------------------|-------|---|-----------------|----|----------------|----|----------------|---|-------------------|-------|-------------------------------------|--------|
|                          | R     | L | h               | b  | L <sub>1</sub> | f  | h <sub>1</sub> | e |                   |       |                                     |        |
| <b>SCAC R/L1010-H06X</b> | ●     | ● | 10              | 10 | 100            | 10 | 10             | 0 | CC□T0602          | 1.5   | TRX08                               |        |
| <b>SCAC R/L1215-K09X</b> | ●     | ● | 12              | 15 | 125            | 15 | 12             | 0 | CC□T09T3          | 3.4   | TRX15                               |        |
| <b>SCAC R/L1215-F09X</b> | ●     | ● | 12              | 15 | 85             | 15 | 12             | 0 | CC□T09T3          |       |                                     |        |

85mm Shank

Insert selection From D25

Small Product Machining