

### Diamond handy files

Diamond handy files have a forged shank which allows the use without an additional handle.

PFERDVALUE:



Profile	Cross section with coating [mm]	Overall length [mm]	Coating length [mm]	Grit size		Description
				D 126	D 181	
				EAN 4007220		
hand	10.3 x 2.8	215	100	017302	535455	1 DF 2601 ...
half-round	12.5 x 3.8	215	100	017319	535462	1 DF 2602 ...
three square	10	215	100	017326	535479	1 DF 2607 ...
square	5.5 x 5.5	215	100	017333	535486	1 DF 2608 ...
round	6.7	215	100	017340	535493	1 DF 2610 ...

### Diamond handy file sets

Diamond handy file sets are supplied in a sturdy, practical plastic box which protects the tools from damage. This is ideal for keeping in the tool trolley or workbench.

Contents:

- 1 piece each:
- DF 2601 (hand)
- DF 2602 (half-round)
- DF 2607 (three square)
- DF 2608 (square)
- DF 2610 (round)

PFERDVALUE:



Grit size		Description
D 126	D 181	
EAN 4007220		
017357	535585	1 DF 2627 ...

### Conical diamond files

#### Conical diamond files

The conical diamond files are used on particularly narrow, deep contours in toolmaking. Because of the forged shank, they can be used without a handle.



Width A [mm]	Thickness B [mm]	Thickness B <sub>1</sub> [mm]	Overall length [mm]	Coating length [mm]	Grit size			Description
					D 46	D 91	D 126	
					EAN 4007220			
4.0	2.0	0.5	170	50	070635	070659	070666	1 DF-K 170-4-2-0,5 ...
6.0	2.4	0.5	170	50	070673	070680	070697	1 DF-K 170-6-2,4-0,5 ...
8.0	2.4	0.5	170	50	070703	070710	070727	1 DF-K 170-8-2,4-0,5 ...
10.0	2.5	0.5	170	50	070734	070741	070758	1 DF-K 170-10-2,5-0,5 ...