


Cross Roller Guide

Cross Roller Table SCVRU Type

SCVRU1 Type



Model No.	Max Stroke	Major Dimensions				Top Dimensions												
		W -0.2 -0.4	T ± 0.1	L	Mass [kg]	J	$n \times F$	G	S	J ₁	$n_1 \times F_1$	G ₁	G ₂	b ₁	T ₃	$S_1 \times \varnothing$	T ₂	T ₁
SCVRU 1025	12	30	17	25	0.08	10	-	12.5	M2	18.4	-	7.5	2.5	12	2.5	M2x4	11	5.5
SCVRU 1035	18			35	0.11		1x10				4.5							
SCVRU 1045	25			45	0.15		2x10				6							
SCVRU 1055	32			55	0.18		3x10				7.5							
SCVRU 1065	40			65	0.21		4x10				8.5							
SCVRU 1075	45			75	0.24		5x10				11							
SCVRU 1085	50			85	0.27		6x10				13.5							