


# CoroMill® 245 insert for milling

KRINS 45°



	RE	BS	Ordering code	P		M		K		N		S		H		Dimensions, mm inch						
				IC	LE	S	IC	LE	S	IC	LE	S	IC	LE	S	IC	LE	S				
Light	12	2.3	R245-12 T3 E-AL														13.4	10.0	3.97			
		.091															.528	.394	.156			
	12	1.5	R245-12 T3 E-PL	☆	☆							☆	☆			☆	☆	☆	☆			
		.059	.083																			
Light	12	1.5	R245-12 T3 M-PL	☆	☆	☆	☆	☆					☆	☆			☆	☆	☆			
		.059	.081																			
	12	1.5	R245-12 T3 E-ML	☆	☆				☆				☆	☆			☆	☆				
		.059	.083																			
Light	12	1.5	R245-12 T3 E-KL						☆	☆	☆			☆	☆							
		.059	.083																			
		1.5	R245-12 T3 M-KL						☆	☆	☆					☆						
		.059	.079																			
Medium	12	1.5	R245-12 T3 M-PM	☆	☆	☆	☆	☆					☆	☆			☆	☆	☆	☆		
		.059	.081																			
	18	1.0	R245-18 T6 M-PM	☆	☆	☆	☆	☆					☆	☆			☆	☆	☆	☆		
		.039	.059																			
Medium	12	1.5	R245-12 T3 K-MM					☆				☆				☆	☆					
		.059	.083																			
	18	1.0	R245-18 T6 M-MM	☆				☆	☆					☆	☆							
		.039	.059																			
Medium	12	1.5	R245-12 T3 M-KM					☆	☆	☆	☆				☆							
		.059	.079																			
	18	1.0	R245-18 T6 M-KM					☆	☆	☆	☆				☆							
		.039	.059																			

J474
 GC
 J508
 ISO 13399
 Q1
 C3 - DC
 Q17

**SANDVIK**  
Coromant