



CoroTurn® 107 insert for turning

Rhombic 35°




		ISO CODE	P							M					K			N		S					ANSI CODE								
			1515	1525	4205	4235	4315	4325	5015	GC30	1115	1125	2015	2025	2035	235	GC15	3005	3205	3210	3215	GC30	H13A	1125		H10	H13A	1105	1115	1125	GC15	H13A	S05F
Medium		11 1/4 VCMT 11 03 04-PM	☆	☆	☆	☆	☆																										VCMT 221-PM
		VCMT 11 03 08-PM	☆																														VCMT 222-PM
		16 3/8 VBMT 16 04 04-MM								☆	☆	☆	☆	☆													☆	☆	☆				VBMT 331-MM
		VBMT 16 04 08-MM								☆	☆	☆	☆	☆													☆	☆	☆				VBMT 332-MM
		VBMT 16 04 12-MM								☆	☆	☆	☆	☆													☆	☆				VBMT 333-MM	
		11 1/4 VCMT 11 03 04-MM								☆		☆																					VCMT 221-MM
VCMT 11 03 08-MM												☆																				VCMT 222-MM	
	16 3/8 VBMT 16 04 04-KM															☆		☆	☆	☆	☆											VBMT 331-KM	
	VBMT 16 04 08-KM															☆		☆	☆	☆	☆											VBMT 332-KM	
	VBMT 16 04 12-KM															☆		☆	☆	☆	☆											VBMT 333-KM	
	11 1/4 VCMT 11 03 08-KM																		☆													VCMT 222-KM	
	16 3/8 VBGT 16 04 01-UM								☆	☆										☆	☆			☆	☆	☆	☆	☆				VBGT 3303-UM	
	VBGT 16 04 02-UM	☆							☆	☆										☆	☆			☆	☆	☆	☆	☆				VBGT 330-UM	
	VBGT 16 04 04-UM	☆							☆	☆										☆	☆			☆	☆	☆	☆	☆				VBGT 331-UM	
	VBGT 16 04 08-UM	☆							☆	☆										☆	☆			☆	☆	☆	☆	☆				VBGT 332-UM	


For dimensions, see code key on page I14.



A13



A27



A558



I1