

Carbide Blanks

Shape	Cat. No.	Stock Carbide										Dimensions (mm)				Applicable Brazed Tools		
		P (Steel)					M (Stainless Steel)		K (Cast Iron)					A	B		C	r _ε
		P10	P20	P30	P40		M20	M40	K01	K01	K10	K20	K20					
	01-0	●	●	●			●	●		●	●	●	●	10	6	3	4	31 Type 32 Type 45 Type 46 Type
	01-1	●	●	●			●	●		●	●	●	●	13	9	3	5	
	01-2	●	●	●			●	●		●	●	●	●	16	11	4	5	
	01-3	●	●	●	▲		●	●		●	●	●	●	19	13	5	5	
	01-4	●	●	●			●	●		●	●	●	●	22	15	6	8	
	01-5													25	17	7	8	
	01-6													30	20	8	8	
	02-0	●	●	●			●	●		●	●	●	●	10	6	3	—	41 Type 42 Type
	02-1	●	●	●			●	●		●	●	●	●	13	9	3	—	
	02-2	●	●	●	●		●	●		●	●	●	●	16	11	4	—	
	02-3	●	●	●	●		●	●		●	●	●	●	19	13	5	—	
	02-4	●	●	●	▲		●	●		●	●	●	●	22	15	6	—	
	02-5													25	17	7	—	
	02-6													30	20	8	—	
	03-0	●	●									●	10	—	3	—	37 Type 38 Type 47 Type 48 Type	
	03-1	●	●				●	●		●	●	●	●	12	—	3		—
	03-2	●	●	●			●	●		●	●	●	●	15	—	4		—
	03-3	●	●	●			●	●		●	●	●	●	18	—	5		—
	03-4		●	●			●	●			●	●		24	—	6		—
	03-5													24	—	7		—
	03-6													28	—	8		—
	04-0	●	●	●			●	●		●	●	●	●	10	6	3	4	33 Type 34 Type
	04-1	●	●	●			●	●		●	●	●	●	13	9	3	5	
	04-2	●	●	●	▲		●	●		●	●	●	●	16	11	4	5	
	04-3	●	●	●			●	●		●	●	●	●	19	13	5	5	
	04-4	●	●	●			●	●		●	●	●	●	22	15	6	8	
	04-5													25	17	7	8	
	04-6													30	20	8	8	
	05-1	●	●	●			●	●		●	●	●	●	5	8	3	—	49 Type 50 Type 51 Type 52 Type
	05-2	●	●	●			●	●		●	●	●	●	6	10	4	—	
	05-3	●	●	●			●	●		●	●	●	●	7	12	5	—	
	05-4	●	●	●			●	●		●	●	●	●	9	16	6	—	
	05-5													10	18	7	—	
	05-6													11	20	8	—	

K
Carbide Materials
Brazed Tools