


# Cylindrical shank to CoroTurn® SL adapter



## Metric version

|                   |                   |     |     |      |      |               | Dimensions         |                    |    |     |     |    |    |       |    |      | CP BarPSI |  | Kg |
|-------------------|-------------------|-----|-----|------|------|---------------|--------------------|--------------------|----|-----|-----|----|----|-------|----|------|-----------|--|----|
| CZC <sub>MS</sub> | CZC <sub>WS</sub> | OHN | OHX | CNSC | CXSC | Ordering code | DCON <sub>MS</sub> | DCON <sub>WS</sub> | H  | LPR | LF  | WF | HF | CNT   |    |      |           |  |    |
| 16                | 16                | 0   | 64  | 1    | 1    | 570-2C 16 105 | 16                 | 16                 | 15 | 105 | 105 | 0  | 0  | G1/8" | 70 | 0.1  |           |  |    |
| 20                | 20                | 0   | 80  | 1    | 1    | 570-2C 20 140 | 20                 | 20                 | 18 | 140 | 140 | 0  | 0  | G1/4" | 70 | 0.3  |           |  |    |
| 25                | 25                | 0   | 100 | 1    | 1    | 570-2C 25 200 | 25                 | 25                 | 23 | 200 | 200 | 0  | 0  | G1/4" | 70 | 0.7  |           |  |    |
| 32                | 32                | 0   | 128 | 1    | 1    | 570-2C 32 218 | 32                 | 32                 | 30 | 218 | 218 | 0  | 0  | G3/8" | 70 | 1.2  |           |  |    |
| 40                | 40                | 0   | 160 | 1    | 1    | 570-2C 40 283 | 40                 | 40                 | 37 | 283 | 283 | 0  | 0  | G1/2" | 70 | 2.9  |           |  |    |
| 50                | 50                | 0   | 200 | 1    | 1    | 570-2C 50 360 | 50                 | 50                 | 47 | 360 | 360 | 0  | 0  | G1/2" | 70 | 15.2 |           |  |    |
| 60                | 60                | 0   | 240 | 1    | 1    | 570-2C 60 460 | 60                 | 60                 | 57 | 460 | 460 | 0  | 0  | G1/2" | 70 | 15.1 |           |  |    |

## Inch version

|                   |                   |       |        |      |      |                   | Dimensions, inch   |                    |       |        |        |      |      |      |      |      | CP BarPSI |  | Lbs |
|-------------------|-------------------|-------|--------|------|------|-------------------|--------------------|--------------------|-------|--------|--------|------|------|------|------|------|-----------|--|-----|
| CZC <sub>MS</sub> | CZC <sub>WS</sub> | OHN   | OHX    | CNSC | CXSC | Ordering code     | DCON <sub>MS</sub> | DCON <sub>WS</sub> | H     | LPR    | LF     | WF   | HF   | CNT  |      |      |           |  |     |
| 5/8               | 16                | .000  | 2.500  | 1    | 1    | A570-2C D10 04-16 | .625               | .630               | .560  | 4.210  | 4.210  | .000 | .000 | G1/8 | 1015 | 0.2  |           |  |     |
| 3/4               | 20                | 1.732 | 3.000  | 1    | 1    | A570-2C D12 05-20 | .750               | .787               | .710  | 5.200  | 5.200  | .000 | .000 | G1/4 | 1015 | 0.5  |           |  |     |
| 1                 | 25                | 2.402 | 4.000  | 1    | 1    | A570-2C D16 07-25 | 1.000              | .984               | .910  | 7.200  | 7.200  | .000 | .000 | G1/4 | 1015 | 1.4  |           |  |     |
| 1 1/4             | 32                | 2.913 | 5.000  | 1    | 1    | A570-2C D20 09-32 | 1.250              | 1.260              | 1.180 | 8.740  | 8.740  | .000 | .000 | G3/8 | 1015 | 2.3  |           |  |     |
| 1 1/2             | 40                | 3.583 | 6.000  | 1    | 1    | A570-2C D24 11-40 | 1.500              | 1.575              | 1.370 | 10.750 | 10.750 | .000 | .000 | G1/2 | 1015 | 3.5  |           |  |     |
| 2                 | 50                | 4.803 | 8.000  | 1    | 1    | A570-2C D32 14-50 | 2.000              | 1.969              | 1.870 | 14.410 | 14.410 | .000 | .000 | G1/2 | 1015 | 11.3 |           |  |     |
| 2 1/2             | 60                | 6.142 | 10.000 | 1    | 1    | A570-2C D40 18-60 | 2.500              | 2.362              | 2.380 | 18.430 | 18.430 | .000 | .000 | G1/2 | 1015 | 11.3 |           |  |     |

EasyFix for 16-25 mm ( .625-1.000 inch)



I1



I38

