

Face Mill WGC (M/F) Type

General Milling for Steel, Cast Iron & Exotic Material



Fig. 1




Fig. 2





Fig. 3



- Body
- Standard WGC - Type

Cat. No.	Stock	Dimensions (mm)										No. of Teeth	Weight (Kg)	Fig.
		DC	DCX	DCSFMS	LF	KWW	KDP	DCB	D2	D1	CBDP			
WGC 3032 RS	▲	32	41	32	40	8,4	5,6	16	9	14	18	4	0,2	1
3040 RS	▲	40	49	32	40	8,4	5,6	16	9	14	18	4	0,3	1
3050 RS	▲	50	59	40	40	10,4	6,3	22	11	18	20	5	0,4	1
3063 RS	▲	63	72	50	40	10,4	6,3	22	11	18	20	6	0,6	1
3080 RS	▲	80	89	60	50	12,4	7,0	27	13,5	20	25	6	1,1	1
WGC 3100 RS		100	109	70	50	14,4	8,5	32	-	-	32	7	1,5	2
WGC 4040 RS	▲	40	52	32	40	8,4	5,6	16	9	14	18	3	0,4	1
4050 RS	▲	50	63	40	40	10,4	6,3	22	11	18	20	3	0,5	1
4063 RS	▲	63	76	50	40	10,4	6,3	22	11	18	20	4	0,6	1
4080 RS	▲	80	93	60	50	12,4	7,0	27	13,5	20	25	4	1,0	1
WGC 4100 RS	▲	100	113	70	50	14,4	8,5	32	-	-	32	5	1,5	2
4125 RS	▲	125	138	80	63	16,4	9,5	40	-	-	38	6	2,6	2
4160 RS	▲	160	173	100	63	16,4	9,5	40	-	-	38	7	4,0	2
WGC 4200 RS	▲	200	213	130	63	25,7	14,0	60	-	-	35	8	6,6	3

- Medium Pitch WGCM - Type

Cat. No.	Stock	Dimensions (mm)										No. of Teeth	Weight (Kg)	Fig.
		DC	DCX	DCSFMS	LF	KWW	KDP	DCB	D2	D1	CBDP			
WGCM 4050 RS	▲	50	63	40	40	10,4	6,3	22	11	18	20	4	0,5	1
4063 RS	▲	63	76	50	40	10,4	6,3	22	11	18	20	5	0,6	1
4080 RS	▲	80	93	60	50	12,4	7,0	27	13,5	20	25	6	1,0	1
WGCM 4100 RS	▲	100	113	70	50	14,4	8,5	32	-	-	32	7	1,5	2
4125 RS	▲	125	138	80	63	16,4	9,5	40	-	-	38	8	2,6	2
4160 RS	▲	160	173	100	63	16,4	9,5	40	-	-	38	10	4,0	2
WGCM 4200 RS	▲	200	213	130	63	25,7	14,0	60	-	-	35	12	6,6	3

- Fine Pitch WGCF - Type

Cat. No.	Stock	Dimensions (mm)										No. of Teeth	Weight (Kg)	Fig.
		DC	DCX	DCSFMS	LF	KWW	KDP	DCB	D2	D1	CBDP			
WGCF 4050 RS	▲	50	63	40	40	10,4	6,3	22	11	18	20	5	0,5	1
4063 RS	▲	63	76	50	40	10,4	6,3	22	11	18	20	6	0,6	1
4080 RS	▲	80	93	60	50	12,4	7,0	27	13,5	20	25	8	1,0	1
WGCF 4100 RS	▲	100	113	70	50	14,4	8,5	32	-	-	32	10	1,5	2
4125 RS	▲	125	138	80	63	16,4	9,5	40	-	-	38	12	2,6	2
4160 RS	▲	160	173	100	63	16,4	9,5	40	-	-	38	16	4,0	2
WGCF 4200 RS	▲	200	213	130	63	25,7	14,0	60	-	-	35	20	6,6	3

■ Spare Parts

Cutter	Shim	Shim screw	Insert screw	Wrench	Wrench
WGC 3000 RS	-	-	BFTX 0307 IP	2,0 TRDR 10 IP	-
WGC/F 4000 RS	WGCS 13 R	BW 0507 F	BFTX 03512 IP	3,0 TRDR 15 IP	LH035

■ Structure



▲ = To be replaced by new item

Recommended Tightening Torque (N·m)