



External Turning



Parts


	
	(For Torx Holes)
Screw	Wrench
TFR33○○	BFTX0410NSW RT08

Holder

Cat. No.	Stock	Dimensions (mm)						Applicable Insert
		h	b	L ₁	f	h ₁	h ₂	
SFT R1010	●	10	10	120	10	10	3	TFR33○○
SFT R1212	●	12	12	120	12	12	1	
SFT R1616	●	16	16	120	16	16	—	
SFT R2020	●	20	20	120	20	20	—	

Insert

Cat. No.	Stock	Dimensions (mm)			Holder
	ACZ150	ød	w	r _ε	
TF R3300	●	9.525	4.76	—	SFT R○○○○
TF R3305	●	9.525	4.76	0.05	
TF R3315	●	9.525	4.76	0.15	
TF R3320	●	9.525	4.76	0.20	



*1 Max. depth-of-cut is 4.0 mm.
*2 Indicates angle when setting the holder.