





# Zero Off-set Holders



■ Holder



Above figures show right hand tools.

Cat. No.	Stock		Dimensions (mm)						Applicable Insert
	R	L	h	b	L <sub>1</sub>	f	h <sub>1</sub>	e	
SVJC R/L1010-H11X	●	●	10	10	100	10	10	0	VC□T1103
SVJC R/L1212-K11X	●	●	12	12	125	12	12	0	VC□T1103
SVJC R/L1212-F11X	●	●	12	12	85	12	12	0	VC□T1103

■ Parts

Screw	Recommended Tightening Torque (N·m)	Wrench
BFTX02508NV	1.5	TRX08

Insert selection D32



■ Holder

Cat. No.	Stock	Dimensions (mm)								Applicable Insert
		h	b	L <sub>1</sub>	f	h <sub>1</sub>	h <sub>2</sub>	b <sub>3</sub>	e	
PTXN R1016-X16X	●	10	16	120	20	10	2	4	0	TN□□1604
PTXN R1216-X16X	●	12	16	120	20	12	0	4	0	TN□□1604
PTXN R1616-X16X	●	16	16	120	20	16	0	4	0	TN□□1604
PTXN R2020-X16X	●	20	20	120	20	20	0	0	0	TN□□1604

■ Parts

Lever Pin	Screw	Wrench
LCL33NT	LCS33NT	LH020NT

Insert selection From B54

Small Product Machining