













# Screws

## Screws

	Adjust Bolt	Cat. No.	Stock	Dimensions (mm)						Torque (N-m)	
		<b>SRFJ</b>	●	M4	0.7	17	6.5	6	2	—	
	Adjust Bolt	Cat. No.	Stock	Dimensions (mm)						Torque (N-m)	
		<b>FMUJ</b>	●	M4	0.7	17	6.5	6	1	—	
	Fastener Bolt	Cat. No.	Stock	Dimensions (mm)						Torque (N-m)	
		<b>FBX0811</b>	●	M8	1.25	11	4.9	8.5	4	—	
		<b>FBX0817</b>	●	M8	1.25	17	5	8.5	4	—	
 <p style="text-align: center;">BT0507K Shape</p> 	Set Screw Hexagonal Hole Type	Cat. No.	Stock	Dimensions (mm)						Torque (N-m)	
		<b>BT0306</b>	●	M3	0.5	6	—	1.5	—	—	
		<b>BT0404</b>	●	M4	0.7	4	—	2	—	—	
		<b>BT0406</b>	●	M4	0.7	6	—	2	—	—	
		<b>BT0408</b>	●	M4	0.7	8	—	2	—	—	
		<b>BT0412</b>	●	M4	0.7	12	—	2	—	—	
		<b>BT0506</b>	●	M5	0.8	6	—	2.5	—	—	
		<b>BT0507K</b>	●	M5	0.8	7	—	2.5	—	—	
		<b>BT0610</b>	●	M6	1.0	10	—	3	—	—	
		<b>BT0612</b>	●	M6	1.0	12	—	3	—	—	
		<b>BT0620</b>	●	M6	1.0	20	—	3	—	—	
		<b>BT06035T</b>	●	M6	1.0	3.5	—	T15	—	—	
			Flat Head Screw	Cat. No.	Stock	Dimensions (mm)					
<b>FBUP1-A0-8</b>	●			M3	0.5	6	4.4	2	82	<b>1.0</b>	
<b>FBUP2-A0-8</b>	●			M3	0.5	10	5.5	2	82	<b>1.0</b>	
<b>FBUP3-A0-8</b>	●			M3.5	0.6	12	7	2	82	<b>1.0</b>	
<b>FBUP4-A0-8</b>	●			M5	0.8	15	9.3	3	82	<b>2.7</b>	
<b>BFX0307R</b>	●			M3	0.5	7	4	2	60	<b>1.0</b>	
<b>BFX0407R</b>	●			M4	0.7	6.5	5.8	2.5	90	<b>1.8</b>	
<b>BFX0410R</b>	●			M4	0.7	9.5	5.8	2.5	90	<b>1.8</b>	
<b>BFX0410L</b>	●			M4-LH	0.7	9.5	5.8	2.5	90	<b>1.8</b>	
<b>BFX0508</b>	●			M5	0.8	8	7.5	3	90	<b>2.7</b>	
<b>BFX0511R</b>	●			M5	0.8	10.5	7.5	3	90	<b>2.7</b>	
<b>BFX0511L</b>	●			M5-LH	0.8	10.5	7.5	3	90	<b>2.7</b>	
<b>BFX0611R</b>	●			M6	1.0	11	9.5	3	90	<b>2.7</b>	
<b>BXF0520R</b>	●			M5	0.8	25	8.5	4	90	<b>7.0</b>	
<b>BXF0618</b>	●			M6	1.0	18	9	4	90	—	
<b>BXF0616</b>	●	M6	1.0	16	9	4	90	—			
<b>BXF0620</b>	●	M6	1.0	20	14	9	90	—			
* : Left-hand threads											
	Set Screw (For SEC Ballnose Endmills)	Cat. No.	Stock	Dimensions (mm)						Torque (N-m)	
		<b>BTT0407</b>	●	M4	0.5	7	2.6	—	2	60	—
		<b>BTT0411</b>	●	M4	0.5	11	2.6	—	2	60	—
		<b>BTT0511</b>	●	M5	0.8	11	5	—	2	20	—
		<b>BTT0615</b>	●	M6	1.0	15	6	—	2.5	20	—
	Button Head Screw (For SEC Ballnose Endmills)	Cat. No.	Stock	Dimensions (mm)						Torque (N-m)	
		<b>BHF0203L</b>	●	M2-LH	0.4	4	3	1.5	90	—	
* : Left-hand threads											
	Button Head Screw (R Shape)	Cat. No.	Stock	Dimensions (mm)						Torque (N-m)	
		<b>BHF0306R</b>	●	M3	0.5	6.5	4.4	2	90	<b>1.0</b>	
		<b>BHF0306L</b>	●	M3	0.5	6.5	4.4	2	90	—	
		<b>BHF0308R</b>	●	M3	0.5	8	4.4	2	90	<b>1.0</b>	
		<b>BHF0623</b>	●	M6	1.0	23	12	4	90	<b>7.0</b>	
* : Left-hand threads R: Right-hand thread L: Left-hand thread											

## Screws

	Special Cap Screw	Cat. No.	Stock	Dimensions (mm)							Torque (N-m)
		<b>QBX120</b>	●	M12	1.75	54	30	22	10	14	—
<b>QBX160</b>	●	M16	2.0	56	30	28	14	16	—		
	Torx Flat Head Screw	Cat. No.	Stock	Dimensions (mm)							Torque (N-m)
		<b>BFN0206T</b>	●	M2	0.4	5.5	3.3	T8	90	<b>1.1</b>	
		<b>BFN0307T</b>	●	M3	0.5	7	4.2	T10	90	<b>2.0</b>	
		<b>BFN0410T</b>	●	M4	0.7	9.5	5.6	T10	90	<b>2.0</b>	
		<b>BFN0511T</b>	●	M5	0.8	11	7.4	T20	—	—	
		<b>BFS0205T</b>	●	M2	0.4	5.5	3	T8	60	<b>1.1</b>	
		<b>BFTX02508</b>	●	M2.5	0.5	7.5	3.5	T8	60	—	
		<b>BFTX0309</b>	●	M3	0.5	8.8	4.2	T10	60	—	
		<b>BFTX0414</b>	●	M4	0.7	14.5	5.5	T15	60	<b>3.0</b>	
		<b>BFTX0613</b>	●	M6	1.0	13	9	T25	60	—	
		<b>BFTX0615</b>	●	M6	1.0	15	9	T25	60	—	
		<b>BFTX0617</b>	●	M6	1.0	17	9	T25	60	—	
		<b>BFTX016033</b>	●	M1.6	0.35	3.3	2.6	T6	60	<b>0.2</b>	
		<b>BFTX03508</b>	●	M3.5	0.6	8	5.1	T10	52	<b>2.0</b>	
		<b>BFTX03584</b>	●	M3.5	0.6	7.4	5.2	T15	60	<b>3.0</b>	
		<b>BFTX03588</b>	●	M3.5	0.6	8.8	5.2	T15	60	<b>3.4</b>	
		<b>BFTX01604N</b>	●	M1.6	0.35	4.2	2.4	T6	60	<b>0.2</b>	
		<b>BFTX0203N</b>	●	M2	0.4	3	2.7	T6	60	<b>0.5</b>	
		<b>BFTX0204N</b>	●	M2	0.4	4.3	2.7	T6	60	<b>0.5</b>	
		<b>BFTX02205N</b>	●	M2.2	0.45	4.5	3	T6	60	<b>0.5</b>	
		<b>BFTX02505N</b>	●	M2.5	0.45	4.5	3.45	T8	60	<b>1.1</b>	
		<b>BFTX02506N</b>	●	M2.5	0.45	5.5	3.45	T8	60	<b>1.5</b>	
		<b>BFTX0306N</b>	●	M3	0.5	5.8	4.2	T10	60	<b>2.0</b>	
		<b>BFTX0307N</b>	●	M3	0.5	6.5	4.2	T10	60	<b>2.0</b>	
		<b>BFTX03085N</b>	●	M3	0.5	8.3	5.4	T10	60	—	
		<b>BFTX0309N</b>	●	M3	0.5	9	4.2	T10	60	—	
<b>BFTX0312N</b>	●	M3	0.5	12	5.4	T10	60	—			
<b>BFTX0406N</b>	●	M4	0.7	6	5.6	T15	60	—			
<b>BFTX0407N</b>	●	M4	0.7	7	5.6	T15	60	<b>3.0</b>			
<b>BFTX0409N</b>	●	M4	0.7	9	5.6	T15	60	<b>3.4</b>			
<b>BFTX0412N</b>	●	M4	0.7	12	5.6	T15	60	<b>3.0</b>			
<b>BFTX0509N</b>	●	M5	0.8	9	7	T20	60	<b>5.0</b>			
<b>BFTX0511N</b>	●	M5	0.8	11.5	7	T20	60	<b>5.0</b>			
<b>BFTX0513N</b>	●	M5	0.8	13	7	T20	60	<b>5.0</b>			
<b>BFTX0515N</b>	●	M5	0.8	15	7	T20	60	—			
<b>BFTX0615N</b>	●	M6	1.0	15	9	T25	60	<b>7.5</b>			
<b>BFTX0619N</b>	●	M6	1.0	19	9	T25	60	<b>7.5</b>			
<b>BFTX0203A</b>	●	M2	0.4	3.0	2.7	T6	90	<b>0.5</b>			
<b>BFTX0204A</b>	●	M2	0.4	4.3	2.7	T6	90	<b>0.5</b>			
<b>BFTX0305A</b>	●	M3	0.5	5.3	4.3	T10	90	—			
<b>BFTX0306A</b>	●	M3	0.5	5.8	4.3	T10	90	<b>2.0</b>			
<b>BFTX0307A</b>	●	M3	0.5	6.8	4.3	T10	90	<b>2.0</b>			
<b>BFTX0407A</b>	●	M4	0.7	7.3	5.6	T15	90	<b>3.4</b>			
<b>BFTX0410A</b>	●	M4	0.7	10.3	5.6	T15	90	<b>3.4</b>			
<b>BFTX0509A</b>	●	M5	0.8	9.3	6.9	T20	90	<b>5.0</b>			
<b>BFTY02205</b>	●	M2.2	0.5	5	3.1	T7	60	—			
<b>BFTY02206</b>	●	M2.2	0.45	5.6	3.05	T7	60	<b>1.0</b>			
	Torx Double Screw	Cat. No.	Stock	Dimensions (mm)							Torque (N-m)
		<b>BFTX0410T8R</b>	●	M4	0.7	9.6	5.6	T8	60	<b>1.1</b>	
		<b>BFTX0410T8L</b>	●	M4	0.7	9.6	5.6	T8	60	<b>1.1</b>	
* : Left-hand threads R: Right-hand thread L: Left-hand thread											