Reed Auto Switch Direct Mounting Type D-A90(V)/D-A93(V)/D-A96(V) (€

Grommet D-A93 D-A90 (V) D-A93V D-A96 (V)

∧Caution

Precautions

Fix the auto switch with the existing screw installed on the auto switch body. The auto switch may be damaged if a screw other than the one supplied is used.

Auto Switch Specifications

the products conforming to the international standards.

(g)

	PLC: Programmable Logic Controller							
D-A90, D-A90V (Without indicator light)								
Auto switch model	D-A90, D-A90V							
Applicable load	IC circuit, Relay, PLC							
Load voltage	24 V AC or less	48 V C or less	100 V AC or less					
Maximum load current	50 mA	40 mA	20 mA					
Circuit diagram*	4							
Contact protection circuit	None							
Internal resistance	1 Ω or less (Including lead wire length of 3 m)							
Standard	CE marking							
D-A93, D-A93V, D-A96, D-A96V (With indicator light)								
Auto switch model	D-A93, D-A93V		D-A96, D-A96V					
Applicable load	Relay, PLC		IC circuit					
Load voltage	24 VDC(4)	100 VAC	4 to 8 VDC					
Load current range and Maximum load current (3)	5 to 40 mA	5 to 20 mA	20 mA					
Circuit diagram*		(5)						
Contact protection circuit	None							
Internal voltage drop	D-A93: 2.4 V or less (up to 20 mA)/3 V or less (up to 40 mA) D-A93V: 2.7 V or less		0.8 V or less					
Indicator light	Red LED illuminates when turned ON.							
Standard	CE marking							

Oilproof Heavy-duty Lead Wire Specifications

Auto switch model		D-A90(V)	D-A93(V)	D-A96(V)		
Sheath	Outside diameter [mm]	ø2.7				
Insulator	Number of cores	2 cores (Brown/Blue)		3 cores (Brown/Blue/Black)		
	Outside diameter [mm]	ø	ø0.91			
Conductor	Effective area [mm²]	0.18		0.15		
	Strand diameter [mm]	ø0.08				
Lead wire minimum bending radius [mm] (Reference values)		17				

* Refer to the circuit diagram no. on page 1587. Note 1) Refer to page 1584 for reed auto switch common specifications.

Note 2) Refer to page 1584 for lead wire lengths.

Note 3) Under 5 mA, the strength of the indicator light is poor. In some cases, visibility of the indicator light will not be possible where the output signal is less than 2.5 mA. However, there is no problem in terms of contact output, when an output signal exceeds 1 mA or more.


Note 4) The auto switches can operate at 12 VDC, but consider the internal voltage drop of the auto switch described in Reed Auto Switch Precautions on page 12.


Weight

Model		D-A90	D-A90V	D-A93	D-A93V	D-A96	D-A96V
Lead wire length	0.5 m (NiI)	6	6	6	6	8	8
	1 m (M)	_	_	11	_	_	_

Dimensions (mm) D-A90/D-A93/D-A96 D-A90V/D-A93V/D-A96V

5 m (Z)





47

47