

# Screws

## Screws

Double Screw	Cat. No.	Stock	Dimensions (mm)					Torque (N-m)		
			d	Pitch	L	ℓ	D		B	
	WB4-8	●	M4	0.7	7.5	3	3.0	2	—	
	WB5-10	●	M5	0.8	10	4	3.8	2.5	—	
	WB5-12	●	M5	0.8	12	5	3.8	2.5	—	
	WB6-10	●	M6	1.0	10	3.5	4.5	3	—	
	WB6-13	●	M6	1.0	13	5	4.5	3	—	
	WB6-16	●	M6	1.0	16	6	4.5	3	—	
	WB6-20	●	M6	1.0	20	8.5	4.5	3	—	
	WB6-30	●	M6	1.0	30	12	4.5	3	—	
	WB8-20	●	M8	1.25	20	8.5	6.2	4	—	
	WB8-24	●	M8	1.25	24	8.5	6.2	4	—	
WB8-30	●	M8	1.25	30	11.5	6.2	4	—		
WB8F-30	●	M8	1.0	30	11.5	6.2	4	—		
Double Screw (Single Torx)	Cat. No.	Stock	Dimensions (mm)					Torque (N-m)		
<p>Cat. No. Suffixes: T indicates right-hand thread, TL indicates left-hand thread</p> <p>Cat. No. Suffixes: T indicates left-hand thread, TL indicates right-hand thread</p>	WB6-16T	●	M6	1.0	16	6	4.5	T20	—	
	WB6-20T	●	M6	1.0	20	8.5	4.5	T20	—	
	WB6-20TL	●	M6	1.0	20	8.5	4.5	T20	—	
	WB7-15T	●	M7	1.0	15	5.5	5	T25	—	
	WB7F-15T	●	M7	0.75	15	5.5	5	T25	—	
	WB8R-16T	●	M8	1.25	14	6	6.2	T27	—	
	WB8L-16T	●	M8	1.25	14	6	6.2	T27	—	
	WB7F-20TL	●	M7	0.75	20	8.5	5.5	T25	—	
	WB8-22T	●	M8	1.25	22	8.5	6.2	T27	—	
	WB8-22TL	●	M8	1.25	22	8.5	6.2	T27	—	
	WB8-30T	●	M8	1.25	30	11.5	6.2	T27	—	
	WB8-30TL	●	M8	1.25	30	11.5	6.2	T27	—	
	Cap Screw (Hex)	Cat. No.	Stock	Dimensions (mm)					Torque (N-m)	
		BX0304	●	M3	0.5	4	Full	5.5	2.5	—
		BX0308	●	M3	0.5	8	Full	5.5	2.5	—
BX0315		●	M3	0.5	15	Full	5.5	2.5	—	
BX0320		●	M3	0.5	20	Full	5.5	2.5	—	
BX0408		●	M4	0.7	8	6	7	3	—	
BX0410		●	M4	0.7	10	8	7	3	—	
BX0414		●	M4	0.7	14	8	7	3	—	
BX0425		●	M4	0.7	25	23	7	3	—	
BX0508		●	M5	0.8	8	Full	8.5	4	—	
BX0510		●	M5	0.8	10	Full	8.5	4	—	
BX0512		●	M5	0.8	12	Full	8.5	4	—	
BX0515		●	M5	0.8	15	Full	8.5	4	—	
BX0520		●	M5	0.8	20	16	8.5	4	5.0	
BX0520T		●	M5	0.8	20	16	8.5	T20	—	
BX0615		●	M6	1.0	15	Full	10	5	—	
BX0620		●	M6	1.0	20	18	10	5	—	
BX0622		●	M6	1.0	22	18	10	5	—	
BX0625		●	M6	1.0	25	18	10	5	—	
BX0820	●	M8	1.25	20	Full	13	6	—		
Torx Hole Type										
	"T" after the part number indicates "Torx hole"									
Set Screw (Hex)	Cat. No.	在庫	Dimensions (mm)					Torque (N-m)		
	BTD0408	●	M4	0.7	8	2	2.8	2	—	
	BTD0410	●	M4	0.7	10	2	2.8	2	—	
	BTD0412	●	M4	0.7	12	2	2.8	2	—	
	BTD0508	●	M5	0.8	8	3	3.5	2.5	—	
	BTD05F09	●	M5	0.5	9	2	4	T15	—	
	BTD0510	●	M5	0.8	10	3	3.5	2.5	—	
	BTD0518	●	M5	0.8	18	4	3.5	2.5	—	
	BTD0609	●	M6	1.0	9	2	4	3	—	
	BTD0615	●	M6	1.0	15	5	4	3	—	
	BTD0618	●	M6	1.0	18	5	4	3	—	
	BTD0620	●	M6	1.0	20	5	4	3	—	
	BTD0812	●	M8	1.25	12	2	5	4	—	
	BTD0818	●	M8	1.25	18	6	5	4	—	
	BTD0820	●	M8	1.25	20	6	5	4	—	
	BTD0825	●	M8	1.25	25	8.5	5	4	—	
BTD0615T	●	M6	1.0	15	5	4.3	T20	—		
BTD0620T	▲	M6	1.0	20	5	4	T20	—		

## Screws

Button Head Cap Screw	Cat. No.	Stock	Dimensions (mm)					Torque (N-m)	
			d	Pitch	L	ℓ	D		B
	BH0304	●	M3	0.5	4	Full	5.5	2	—
	BH0306	●	M3	0.5	6	Full	5.5	2	—
	FBUP3-A0-9 (BH0308 相当)	●	M3	0.5	8	Full	5.5	2	1.0
	BH0310	●	M3	0.5	10	Full	5.5	2	—
	BH03504	●	M3.5	0.6	4	Full	7	2	—
	BH0408	●	M4	0.7	8	Full	6	2.5	—
	BH0410T	●	M4	0.7	10	Full	7.5	T15	—
	BH0415	●	M4	0.7	15	Full	6	2.5	—
	BH0510	●	M5	0.8	10	Full	9.5	3	—
	BH0516	●	M5	0.8	16	14.4	9.5	3	—
	BH0615	●	M6	1.0	15	Full	10.5	4	—
	BH0616	●	M6	1.0	16	14	10.5	4	—
	BH0620	●	M6	1.0	20	Full	10.5	4	—
	BH0824R	●	M8	1.25	24	20	12	4	—
	BH0824L	●	M8	1.25	24	20	12	4	—
BH0825	●	M8	1.25	25	20	12	5	—	
BH0830R	●	M8	1.25	30	26	12	4	—	
BH0830L	●	M8	1.25	30	26	12	4	—	
BH0832	●	M8	1.25	32	26	12	5	—	
BH1030R	●	M10	1.5	30	26	14	5	—	
BH1030L	●	M10	1.5	30	26	14	5	—	
BH1036R	●	M10	1.5	36	32	14	5	—	
BH1036L	●	M10	1.5	36	32	14	5	—	
Hexagonal Hole Type									
	"T" after the part number indicates "Torx hole"								
Torx Hole Type									
	"T" after the part number indicates "Torx hole"								
Special Cap Screw (Hex)	Cat. No.	Stock	Dimensions (mm)					Torque (N-m)	
	BHA0525	●	M5	0.8	25.5	9.5	8.5	3	—
	BHA0625	●	M6	1.0	30	11.3	10.5	4	—
	BHE0407	●	M4	0.7	9.5	2	5.7	2.5	1.8
	BHE0510	●	M5	0.8	13	3	7.7	3	2.7
Lever Lock Bolt	Cat. No.	Stock	Dimensions (mm)					Torque (N-m)	
	LCS2B	●	M3	0.5	10	3.05	3.6	2	—
	LCS3S	●	M6	1.0	15	10	6	2.5	—
	LCS3	●	M6	1.0	17	10	6	2.5	—
	LCS4	●	M8	1.0	21	10	8	3	—
	LCS5	●	M8	1.0	25	12	8	3	—
	LCS6	●	M10	1.0	27.2	14.4	9.8	4	—
	LCS4CA	●	M8	1.0	17.5	10	8	3	—
	LCS5CA	▲	M8	1.0	20.5	12	8	3	—
	LCS8	▲	M12	1.0	36	15.3	11.8	5	—
	LCS10	●	M5	0.8	14.5	8.5	5	2	—
	LCS12	●	M6	1.0	17	9.6	6	2.5	—
	LCS16	●	M6	1.0	21	13.6	6	2.5	—
	LCS20	●	M8	1.0	23.5	13.2	8	3.0	—
	LCS25	●	M10	1.0	30	17.4	10	4.0	—
	LCS32	●	M12	1.0	36	19.3	12	5.0	—
LCS3TE	●	M6	1.0	15.5	8.5	6	2.5	—	
LCS33NT	●	M5	0.8	12	6.2	—	2	—	
Axial Adjustment Bolt	Cat. No.	Stock	Dimensions (mm)					Torque (N-m)	
	AJM4FT	●	M4	0.5	12	5	7.2	2	—
	AJM4F	●	M4	0.5	12	5	8	2	—
	AJM5F	●	M5	0.5	13	5	9	2	—
	AJM6	●	M6	1.0	18	6	10	2.9	—
Axial Adjustment Bolt	Cat. No.	Stock	Dimensions (mm)					Torque (N-m)	
	RFJ	●	M4	0.7	12	6	6	2	—

Spare Parts