


寸法表 Sタイプ

# V-S



単位:mm

呼び番号	軸径 d <sub>1</sub>	内径 d	断面厚さ C	寸法 A	取付前の幅 B	最大許容径 d <sub>2</sub>	最小許容径 d <sub>3</sub>	取付後の幅 B <sub>1</sub>
V-5S	4.5~5.5	4	2	3.9	5.2	d <sub>1</sub> +1	d <sub>1</sub> +6	4.5±0.4
V-6S	5.5~6.5	5	2	3.9	5.2	d <sub>1</sub> +1	d <sub>1</sub> +6	4.5±0.4
V-7S	6.5~8.0	6	2	3.9	5.2	d <sub>1</sub> +1	d <sub>1</sub> +6	4.5±0.4
V-8S	8.0~9.5	7	2	3.9	5.2	d <sub>1</sub> +1	d <sub>1</sub> +6	4.5±0.4
V-10S	9.5~11.5	9	3	5.6	7.7	d <sub>1</sub> +1	d <sub>1</sub> +9	6.7±0.6
V-12S	11.5~13.5	10.5	3	5.6	7.7	d <sub>1</sub> +1	d <sub>1</sub> +9	6.7±0.6
V-14S	13.5~15.5	12.5	3	5.6	7.7	d <sub>1</sub> +1	d <sub>1</sub> +9	6.7±0.6
V-16S	15.5~17.5	14	3	5.6	7.7	d <sub>1</sub> +1	d <sub>1</sub> +9	6.7±0.6
V-18S	17.5~19	16	3	5.6	7.7	d <sub>1</sub> +1	d <sub>1</sub> +9	6.7±0.6
V-20S	19~21	18	4	7.9	10.5	d <sub>1</sub> +2	d <sub>1</sub> +12	9.0±0.8
V-22S	21~24	20	4	7.9	10.5	d <sub>1</sub> +2	d <sub>1</sub> +12	9.0±0.8
V-25S	24~27	22	4	7.9	10.5	d <sub>1</sub> +2	d <sub>1</sub> +12	9.0±0.8
V-28S	27~29	25	4	7.9	10.5	d <sub>1</sub> +2	d <sub>1</sub> +12	9.0±0.8
V-30S	29~31	27	4	7.9	10.5	d <sub>1</sub> +2	d <sub>1</sub> +12	9.0±0.8
V-32S	31~33	29	4	7.9	10.5	d <sub>1</sub> +2	d <sub>1</sub> +12	9.0±0.8
V-35S	33~36	31	4	7.9	10.5	d <sub>1</sub> +2	d <sub>1</sub> +12	9.0±0.8
V-38S	36~38	34	4	7.9	10.5	d <sub>1</sub> +2	d <sub>1</sub> +12	9.0±0.8
V-40S	38~43	36	5	9.5	13.0	d <sub>1</sub> +2	d <sub>1</sub> +15	11.0±1.0
V-45S	43~48	40	5	9.5	13.0	d <sub>1</sub> +2	d <sub>1</sub> +15	11.0±1.0
V-50S	48~53	45	5	9.5	13.0	d <sub>1</sub> +2	d <sub>1</sub> +15	11.0±1.0
V-55S	53~58	49	5	9.5	13.0	d <sub>1</sub> +2	d <sub>1</sub> +15	11.0±1.0
V-60S	58~63	54	5	9.5	13.0	d <sub>1</sub> +2	d <sub>1</sub> +15	11.0±1.0
V-65S	63~68	58	5	9.5	13.0	d <sub>1</sub> +2	d <sub>1</sub> +15	11.0±1.0
V-70S	68~73	63	6	11.3	15.5	d <sub>1</sub> +3	d <sub>1</sub> +18	13.5±1.2
V-75S	73~78	67	6	11.3	15.5	d <sub>1</sub> +3	d <sub>1</sub> +18	13.5±1.2
V-80S	78~83	72	6	11.3	15.5	d <sub>1</sub> +3	d <sub>1</sub> +18	13.5±1.2
V-85S	83~88	76	6	11.3	15.5	d <sub>1</sub> +3	d <sub>1</sub> +18	13.5±1.2
V-90S	88~93	81	6	11.3	15.5	d <sub>1</sub> +3	d <sub>1</sub> +18	13.5±1.2
V-95S	93~98	85	6	11.3	15.5	d <sub>1</sub> +3	d <sub>1</sub> +18	13.5±1.2
V-100S	98~105	90	6	11.3	15.5	d <sub>1</sub> +3	d <sub>1</sub> +18	13.5±1.2
V-110S	105~115	99	7	13.1	18.0	d <sub>1</sub> +4	d <sub>1</sub> +21	15.5±1.5
V-120S	115~125	108	7	13.1	18.0	d <sub>1</sub> +4	d <sub>1</sub> +21	15.5±1.5
V-130S	125~135	117	7	13.1	18.0	d <sub>1</sub> +4	d <sub>1</sub> +21	15.5±1.5
V-140S	135~145	126	7	13.1	18.0	d <sub>1</sub> +4	d <sub>1</sub> +21	15.5±1.5
V-150S	145~155	135	7	13.1	18.0	d <sub>1</sub> +4	d <sub>1</sub> +21	15.5±1.5
V-160S	155~165	144	8	15.0	20.5	d <sub>1</sub> +4	d <sub>1</sub> +24	18.0±1.8
V-170S	165~175	153	8	15.0	20.5	d <sub>1</sub> +4	d <sub>1</sub> +24	18.0±1.8
V-180S	175~185	162	8	15.0	20.5	d <sub>1</sub> +4	d <sub>1</sub> +24	18.0±1.8
V-190S	185~195	171	8	15.0	20.5	d <sub>1</sub> +4	d <sub>1</sub> +24	18.0±1.8
V-199S	195~210	180	8	15.0	20.5	d <sub>1</sub> +4	d <sub>1</sub> +24	18.0±1.8