

Directional Lock Castors —Swivel ⇔ Fixed—

RoHS compliant products.

POINT

- **Swivel⇔Fixed: easily switchable by putting one-touch lock lever on/off.**

- Directional lock is activated automatically when the castor is in motion.
- Locating and adjusting the locking position is not required.



- SISIKU's unique point - **Box style wheel.**
- Smooth swiveling thanks to **double bearing** in the swivel head with ball protection.

USE EXAMPLE

- For various carriers.
- For work bench.
- For roll box pallet.

◎We'll accept your custom-order. Please feel free to contact us.
(Use "Specification Form for Custom-designed castor" at the end of this catalog.)
◎Please feel free to ask about the product weight for each item.



Use example



Operating one-touch lock lever

NJK Swivel castors



NJK-130

NJK-150

NJK-200

• Color/Finish; Zinc plated

NJKB Swivel with stopper



NJKB-130

NJKB-150

NJKB-200

WHEELS ベアリング変更 (SPMを除く) JBB→CB

CB ...Pressed bearing JBB ...Radial ball bearing

See P.62 to P.71 for detailed description.



→P.70

W (SBR)

CB



→P.68

SST (NR)

- Runs more lightly compared with W!
 - Impact resistance: 1.8 times higher than W. Starting performance: 2.5 times better than W.
- NB φ150 and 200 only.

JBB



→P.70

UW (UR)

JBB




→P.63

EUW (Antistatic UR)

- Volume resistance $10^8 \sim 10^9 \Omega \cdot \text{cm}^*$
- *For reference only, not guaranteed.

JBB




→P.70

WUW (Antibacterial UR/White)

- Antibacterial effect, oil resistance and high elasticity.
- Floor saving and non-marking.

JBB



→P.71

WW (BR)

- Cold resistance (-40°C~+90°C)
- Floor saving and non-marking.

CB

LW (BR)

CB