

Shock Absorbing Castors I-B —Advanced coil spring type—

Towing speed up to 20km/h

RoHS compliant products.


POINT

- Designed for **high-speed operation up to 20km/h.** (for reference only)
- **Combination of thrust bearing and tapered roller bearing** in the swivel head helps to **withstand a considerable shock and impact.**
- Grease packed precision ball bearings for wheel and **supporting shaft** of fork.
 - **Smooth and silent rolling** without subsequent lubrication.
- **Low vibration and noise** during running.
- Thanks to shock absorbing function, **impact loading to swivel head and wheel bearings can be lowered, leading to an increased service life of the product.**



USE EXAMPLE

- For carriers pulled at high speed.
 - For carrying precision equipment and parts.
- ◎We'll accept your custom-order. Please feel free to contact us.
(Use "Specification Form for Custom-designed castor" at the end of this catalog.)
- ◎Please feel free to ask about the product weight for each item.



SAJ-TO Swivel castors



SAJ-TO-200

- Color/Finish; Zinc plated

SAJB-TO Swivel with stopper



SAJB-TO-200

SAK-TO Fixed castors



SAK-TO-200

- Color/Finish; Zinc plated

SAKB-TO Fixed with stopper




SAKB-TO-200

ベアリング変更SST JBB→CB

(*ただし、4km/h以上で使用の場合はJBBの使用をお願いします)

WHEELS JBB ...Radial ball bearing

See P.62 to P.71 for detailed description.



- SST (NR)** JBB
- Runs more lightly compared with W!
 - Impact resistance: 1.8 times higher than W. Starting performance: 2.5 times better than W.
- TRAW** JBB
- (Highly durable rubber)
 - (Aluminum wheel center)