



# WW

## ベアリングJBB削除

- Tire: BR (White)
- Wheel center: Steel SPHC-P
- Bearing: ~~CB~~ Pressed bearing  
~~JBB~~ Radial ball bearing **削除**
- Operating temp.: -40°C~+90°C
- Hardness: (HS) 55-60
- Characteristics: High elasticity. Cold resistance.
- Applicable to Castors on: P.13 P.25 P.51 P.53 P.55



|        |               |                |     |    |    |    |      |               |
|--------|---------------|----------------|-----|----|----|----|------|---------------|
| WW-75  | <del>CB</del> | <del>JBB</del> | 75  | 32 | 35 | 10 | 10.5 | 60<br>(580)   |
| WW-100 | CB            | JBB            | 100 | 35 | 42 | 12 | 13.5 | 80<br>(780)   |
| WW-130 | CB            | JBB            | 130 | 42 | 52 | 20 | 14.0 | 140<br>(1370) |
| WW-150 | CB            | JBB            | 150 | 45 | 55 | 20 | 15.0 | 160<br>(1560) |
| WW-200 | CB            | JBB            | 200 | 45 | 55 | 20 | 17.5 | 200<br>(1960) |
| WW-250 | CB            | JBB            | 250 | 50 | 64 | 25 | 20.0 | 260<br>(2540) |

# YN

## (for Compact heavy duty castors)

- Tire: Nylon 6 + Special recycled nylon
- Wheel center: -
- Bearing: ~~JBB~~ Radial ball bearing
- Operating temp.: -40°C~+120°C
- Hardness: (R) 100-115
- Characteristics: Oil resistance.
- Applicable to Castors on: P.19 P.49



|       |     |  |    |      |      |    |   |               |
|-------|-----|--|----|------|------|----|---|---------------|
| YN-50 | JBB |  | 50 | 32.5 | 35.5 | 8  | - | 300<br>(2940) |
| YN-65 | JBB |  | 65 | 36   | 39   | 10 | - | 400<br>(3920) |
| YN-75 | JBB |  | 75 | 39   | 42   | 10 | - | 500<br>(4900) |

# YN

## (for Stainless steel compact heavy duty castors)

- Tire: Nylon 6 + Special recycled nylon
- Wheel center: -
- Bearing: ~~SJBB~~ Stainless steel radial ball bearing
- Operating temp.: -40°C~+120°C
- Hardness: (R) 100-115
- Characteristics: Oil resistance.
- Applicable to Castors on: P.43



|         |                 |  |    |      |      |    |   |               |
|---------|-----------------|--|----|------|------|----|---|---------------|
| YN-50SU | <del>SJBB</del> |  | 50 | 32.5 | 35.5 | 8  | - | 300<br>(2940) |
| YN-65SU | <del>SJBB</del> |  | 65 | 36   | 39   | 10 | - | 400<br>(3920) |
| YN-75SU | <del>SJBB</del> |  | 75 | 39   | 42   | 10 | - | 500<br>(4900) |