


## ストレートタイプアダプター

● Material : Plated steel, Stainless Steel  
● 材質 : SS(三価クロメートメッキ)・SUS304

### SR-17 (同径)





接続口金具 : SR-01・SR-04

\*印のSUSは受注生産 ※印のSUS304は32

呼び径	ねじT <sub>1</sub>	ねじT <sub>2</sub>	Amm	Bmm	dφmm	Lmm	HEXmm
* 3	G 1/8	Rc 1/8	15	13.0	3.0	28.0	14
6	G 1/4	Rc 1/4	17	16.0	5.5	33.0	19
9	G 3/8	Rc 3/8	19	17.5	7.0	36.5	22
12	G 1/2	Rc 1/2	22	20.0	10.0	42.0	27
19	G 3/4	Rc 3/4	25	21.5	16.0	46.5	※36
25	G 1	Rc 1	27	22.5	22.0	49.5	41
32	G1 1/4	Rc1 1/4	30	27.0	28.0	57.0	50
38	G1 1/2	Rc1 1/2	30	27.0	34.0	57.0	60
50	G 2	Rc 2	36	30.0	45.0	66.0	70
* 65	G2 1/2	Rc2 1/2	42	43.0	56.0	85.0	90

### SR-17 (異径)




接続口金具 : SR-01・SR-04

\*印及びSUSは受注生産

呼び径	ねじT <sub>1</sub>	ねじT <sub>2</sub>	Amm	Bmm	dφmm	Lmm	HEXmm
3×6	G 1/8	Rc 1/4	17	13.0	4.0	30.0	19
6×9	G 1/4	Rc 3/8	19	16.0	5.5	35.0	22
9×12	G 3/8	Rc 1/2	22	17.5	7.0	39.5	27
12×19	G 1/2	Rc 3/4	25	20.0	10.0	45.0	36
19×25	G 3/4	Rc 1	27	21.5	16.0	48.5	41
* 25×32	G 1	Rc1 1/4	30	22.5	22.0	52.5	50
* 32×38	G1 1/4	Rc1 1/2	30	27.0	28.0	57.0	60
* 38×50	G1 1/2	Rc 2	36	27.0	34.0	63.0	70

### SR-17 (異径)




接続口金具 : SR-01・SR-04

\*印及びSUSは受注生産

呼び径	ねじT <sub>1</sub>	ねじT <sub>2</sub>	Amm	Bmm	dφmm	Lmm	HEXmm
6×3	G 1/4	Rc 1/8	14	16.0	5.5	30.0	19
9×6	G 3/8	Rc 1/4	17	17.5	7.0	34.0	22
12×9	G 1/2	Rc 3/8	19	20.0	10.0	39.5	27
19×12	G 3/4	Rc 1/2	22	21.5	16.0	43.5	32
25×19	G 1	Rc 3/4	25	22.5	22.0	47.5	36
* 32×25	G1 1/4	Rc 1	27	27.0	28.0	54.0	50
* 38×32	G1 1/2	Rc1 1/4	30	27.0	34.0	57.0	50
* 50×38	G 2	Rc1 1/2	30	30.0	45.0	60.0	60

### SR-18



接続口金具 : SR-01

SUSは受注生産

呼び径	ねじT <sub>1</sub>	ねじT <sub>2</sub>	Amm	dφmm	Lmm	HEXmm
6	G 1/4	Rc 1/4	17	5.5	34	19
9	G 3/8	Rc 3/8	19	7.0	38	22
12	G 1/2	Rc 1/2	22	10.0	43	27
19	G 3/4	Rc 3/4	25	16.0	49	36
25	G 1	Rc 1	27	22.0	53	41
32	G1 1/4	Rc1 1/4	30	28.0	60	50
38	G1 1/2	Rc1 1/2	30	34.0	63	60
50	G 2	Rc 2	36	45.0	71	70

(注意) 予告なしに、品質・性能・改善のため寸法を変更する事があります。