


FOR GENERAL USE


NO.5A Combination Short Auger Bit

Usable with an electric drill, this auger bit is suitable when you require speedy and accurate shallow boring.



NO.5B Combination Short Auger Bit with Brad Point

Convenient for woodworking machines such as drilling machines. Brad point provides accurate positioning for starting the hole. The most suitable for shallow blind holes without penetration.



S=Size O/A=Overall Length T/L=Twist Length SD=Shank-Dia

Unit mm (inch)

Size	O/A Length	Twist Length	Shank-Dia	WT.kg/doz	Size	O/A Length	Twist Length	Shank-Dia	WT.kg/doz
3	80	45	6.35	0.23	21 (13/16)	130	80	10	1.56
4	80	45	6.35	0.25	22 (7/8)	130	80	10	1.68
5	90	50	6.35	0.27	23	130	80	10	1.72
6 (1/4)	90	50	6.35	0.30	24 (15/16)	130	80	10	1.88
7	90	50	6.35	0.32	25 (1")	130	80	10	1.96
8 (5/16)	90	50	6.35	0.38	26	130	80	10	2.00
9	100	60	6.35	0.42	27 (1-1/16)	130	80	10	2.14
10 (3/8)	100	60	6.35	0.46	28	130	80	10	2.20
11 (7/16)	100	60	6.35	0.50	29 (1-1/8)	130	80	10	2.26
12	100	60	6.35	0.52	30 (1-3/16)	130	80	10	2.42
13 (1/2)	120	70	6.35	0.70	31	140	90	12	3.20
14 (9/16)	120	70	6.35	0.72	32 (1-1/4)	140	90	12	3.32
15	120	70	6.35	0.80	33	140	90	12	3.44
16 (5/8)	120	70	6.35	0.88	34	140	90	12	3.60
17	120	70	6.35	0.90	35 (1-3/8)	140	90	12	3.64
18 (11/16)	120	70	6.35	1.04	36	140	90	12	3.96
19 (3/4)	120	70	6.35	1.10	37 (1-7/16)	140	90	12	3.84
20	130	80	10	1.46	38 (1-1/2)	140	90	12	3.96